

CUC-V14-A1RBK-PC - Panel-mount frame



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Panel-mount frame, degree of protection: IP65



Commercial data

Item number	1413985
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNODZ
Catalog page	Page 360 (C-2-2019)
GTIN	4055626082325
Weight per piece (including packing)	8.9 g
Weight per piece (excluding packing)	8.9 g
Customs tariff number	85389099
Country of origin	DE

CUC-V14-A1RBK-PC - Panel-mount frame



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Technical data

Product properties

Product type	Panel-mount frame
Type	Version 14

Data management status

Article revision	04
------------------	----

Insulation characteristics

Degree of pollution	2
---------------------	---

Dimensions

Width	24.1 mm
Height	55.3 mm
Length	33.2 mm

Material specifications

Material	PA 6
Flammability rating according to UL 94	V0
Seal material	NBR
	HNBR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

Mounting

Thread type	()
-------------	----

CUC-V14-A1RBK-PC - Panel-mount frame



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Classifications

ECLASS

ECLASS-11.0	27440210
ECLASS-12.0	27440210
ECLASS-13.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-V14-A1RBK-PC - Panel-mount frame



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com