

PART NUMBER

54F821^Q3A

Rochester Electronics Manufactured Components

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All re-creations are done with the approval of the Original Component Manufacturer. (OCM)

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceeds the OCM data sheet.

Quality Overview

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-38535
 - Class Q Military
 - Class V Space Level

Qualified Suppliers List of Distributors (QSLD)

- Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OCM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.

REVISIONS

LTR	DESCRIPTION	DATE (YR-MO-DA)	APPROVED
A	Update to reflect latest changes in format and requirements. Editorial changes throughout. --les	04-07-29	Raymond Monnin
B	Update drawing as part of 5 year review. -jt	12-01-17	Charles Saffle
C	Update drawing to current MIL-PRF-38535 requirements. - rdc	18-02-26	Charles Saffle
D	Update drawing to latest MIL-PRF-38535 requirements. -jt	23-01-13	James R. Eschmeyer



Revision Status of Sheets


REV																			
SHEET																			
REV	D	D	D	D	D	D	D	D	D	D	D								
SHEET	1	2	3	4	5	6	7	8	9	10	11								

STANDARD MICROCIRCUIT DRAWING THIS DRAWING IS AVAILABLE FOR USE BY ALL DEPARTMENTS AND AGENCIES OF THE DEPARTMENT OF DEFENSE		PREPARED BY Larry T. Gauder	DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990 https://www.dla.mil/LandandMaritime			
		CHECKED BY Tim H. Noh				
APPROVED BY Monica L. Poelking DRAWING APPROVAL DATE 92-02-19		MICROCIRCUIT, DIGITAL, BIPOLAR, ADVANCED SCHOTTKY, TTL, 10-BIT, NONINVERTING REGISTER, MONOLITHIC SILICON				
AMSC N/A		REVISION LEVEL D	SIZE A 67268	CAGE CODE 5962-89438		
			SHEET 1 OF 11			

1. SCOPE

1.1 Scope. This drawing describes device requirements for MIL-STD-883 compliant, non-JAN class level B microcircuits in accordance with MIL-PRF-38535, appendix A.

1.2 Part or Identifying Number (PIN). The complete PIN is as shown in the following example:



1.2.1 Device type. The device type identify the circuit function as follows:

<u>Device type</u>	<u>Generic number</u>	<u>Circuit function</u>
01	54F821	10-bit noninverting register

1.2.2 Case outlines. The case outlines are as designated in MIL-STD-1835 and as follows:

<u>Outline letter</u>	<u>Descriptive designator</u>	<u>Terminals</u>	<u>Package style</u>
L	GDIP3-T24 or CDIP4-T24	24	dual-in-line
K	GDIP2-F24 or CDIP3-F24	24	flat
3	CQCC1-N28	28	square chip carrier

1.2.3 Lead finish. The lead finish is as specified in MIL-PRF-38535, appendix A.

1.3 Absolute maximum ratings.

Supply voltage range (V _{cc})	-0.5 V dc to +7.0 V dc
Input voltage range	-0.5 V dc to +7.0 V dc
Input current range	-30 mA to +5.0 mA
Voltage applied to any output in the disabled state	-0.5 V dc to +5.5 V dc
Voltage applied to any output in the high state	-0.5 V dc to V _{cc}
Current into any output in the low state	40 mA
Storage temperature range	-65°C to +150°C
Maximum power dissipation (P _D)	550 mW 1/
Lead temperature (soldering, 10 seconds)	+300°C
Junction temperature (T _J)	+175°C
Thermal resistance, junction-to-case (θ _{JC})	See MIL-STD-1835

1.4 Recommended operating conditions.

Supply voltage range (V _{cc})	+4.5 V dc to +5.5 V dc
Minimum high level input voltage (V _{IH})	2.0 V dc
Maximum low level input voltage (V _{IL})	0.8 V dc
Maximum input clamp current (I _{IC})	-18 mA
Maximum high level output Current (I _{OH})	-3 mA
Maximum low level output current (I _{OL})	20 mA
Case operating temperature range (T _C)	-55°C to +125°C

1/ Maximum power dissipation is defined as V_{cc} X I_{cc}, and must withstand the added P_D due to short circuit test e.g., los.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

**SIZE
A**

5962-89438

REVISION LEVEL
D

SHEET
2

1.4 Recommended operating conditions - Continued.

t_s High or Low, Dn to CP (t_s):

V_{CC} = 5.0 V dc at +25°C 3.0 ns
V_{CC} = 4.5 to 5.5 V dc at -55°C to +125°C 4.0 ns

t_h High or Low, Dn to CP (t_h):

V_{CC} = 5.0 V dc at +25°C 2.5 ns
V_{CC} = 4.5 to 5.5 V dc at -55°C to +125°C 2.5 ns

t_w High or Low, CP, t_r = 1.0 ns, t_f = 1.0 ns (t_w):

V_{CC} = 5.0 V dc at +25°C 5.0 ns
V_{CC} = 4.5 to 5.5 V dc at -55°C to +125°C 6.0 ns

f_{MAX}, t_r = 1.0 ns, t_f = 1.0 ns:

V_{CC} = 5.0 V dc at +25°C 100 MHz
V_{CC} = 4.5 to 5.5 V dc at -55°C to +125°C 60 MHz

2. APPLICABLE DOCUMENTS

2.1 Government specification, standards, and handbooks. The following specification, standards, and handbooks form a part of this drawing to the extent specified herein. Unless otherwise specified, the issues of these documents are those cited in the solicitation or contract.

DEPARTMENT OF DEFENSE SPECIFICATION

MIL-PRF-38535 - Integrated Circuits, Manufacturing, General Specification for.

DEPARTMENT OF DEFENSE STANDARDS

MIL-STD-883 - Test Method Standard Microcircuits.

MIL-STD-1835 - Interface Standard Electronic Component Case Outlines.

DEPARTMENT OF DEFENSE HANDBOOKS

MIL-HDBK-103 - List of Standard Microcircuit Drawings.

MIL-HDBK-780 - Standard Microcircuit Drawings.

(Copies of these documents are available online at <https://quicksearch.dla.mil/>.)

2.2 Order of precedence. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing takes precedence. Nothing in this document, however, supersedes applicable laws and regulations unless a specific exemption has been obtained.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

**SIZE
A**

5962-89438

REVISION LEVEL
D

SHEET
3

3. REQUIREMENTS

3.1 Item requirements. The individual item requirements shall be in accordance with MIL-PRF-38535, appendix A for non-JAN class level B devices and as specified herein. Product built to this drawing that is produced by a Qualified Manufacturer Listing (QML) certified and qualified manufacturer or a manufacturer who has been granted transitional certification to MIL-PRF-38535 may be processed as QML product in accordance with the manufacturers approved program plan and qualifying activity approval in accordance with MIL-PRF-38535. This QML flow as documented in the Quality Management (QM) plan may make modifications to the requirements herein. These modifications shall not affect form, fit, or function of the device. These modifications shall not affect the PIN as described herein. A "Q" or "QML" certification mark in accordance with MIL-PRF-38535 is required to identify when the QML flow option is used.

3.2 Design, construction, and physical dimensions. The design, construction, and physical dimensions shall be as specified in MIL-PRF-38535, appendix A and herein.

3.2.1 Case outlines. The case outlines shall be in accordance with 1.2.2 herein.

3.2.2 Terminal connections. The terminal connections shall be as specified on figure 1.

3.2.3 Truth table. The truth table shall be as specified on figure 2.

3.2.4 Test circuit and switching waveforms. The test circuit and switching waveforms shall be as specified on figure 3.

3.3 Electrical performance characteristics. Unless otherwise specified herein, the electrical performance characteristics are as specified in table I and shall apply over the full case operating temperature range.

3.4 Electrical test requirements. The electrical test requirements shall be the subgroups specified in table II. The electrical tests for each subgroup are described in table I.

3.5 Marking. Marking shall be in accordance with MIL-PRF-38535, appendix A. The part shall be marked with the PIN listed in 1.2 herein. In addition, the manufacturer's PIN may also be marked. For packages where marking of the entire SMD PIN number is not feasible due to space limitations, the manufacturer has the option of not marking the "5962-" on the device.

3.5.1 Certification/compliance mark. A compliance indicator "C" shall be marked on all non-JAN devices built in compliance to MIL-PRF-38535, appendix A. The compliance indicator "C" shall be replaced with a "Q" or "QML" certification mark in accordance with MIL-PRF-38535 to identify when the QML flow option is used.

3.6 Certificate of compliance. A certificate of compliance shall be required from a manufacturer in order to be listed as an approved source of supply in MIL-HDBK-103 (see 6.6 herein). The certificate of compliance submitted to DLA Land and Maritime-VA prior to listing as an approved source of supply shall affirm that the manufacturer's product meets the requirements of MIL-PRF-38535, appendix A and the requirements herein.

3.7 Certificate of conformance. A certificate of conformance as required in MIL-PRF-38535, appendix A shall be provided with each lot of microcircuits delivered to this drawing.

3.8 Notification of change. Notification of change to DLA Land and Maritime-VA shall be required for any change that affects this drawing.

3.9 Verification and review. DLA Land and Maritime, DLA Land and Maritime's agent, and the acquiring activity retain the option to review the manufacturer's facility and applicable required documentation. Offshore documentation shall be made available onshore at the option of the reviewer.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

**SIZE
A**

5962-89438

REVISION LEVEL
D

SHEET

4

TABLE I. Electrical performance characteristics.

Test	Symbol	Conditions $-55^{\circ}\text{C} \leq T_c \leq +125^{\circ}\text{C}$ unless otherwise specified		Group A subgroups	Device type	Limits		Unit
						Min	Max	
High level output voltage	V_{OH}	$V_{CC} = 4.5 \text{ V}$	$I_{OH} = -3 \text{ mA}$	1, 2, 3	All	2.4		V
Low level output voltage	V_{OL}	$V_{IH} = 2.0 \text{ V}$	$I_{OL} = 20 \text{ mA}$	1, 2, 3	All		0.5	V
Input clamp voltage	V_{IC}	$V_{IL} = 0.8 \text{ V}$	$I_{IC} = -18 \text{ mA}$	1, 2, 3	All		-1.2	V
High level input current	I_{IH1}	$V_{CC} = 5.5 \text{ V}$	$V_{IN} = 2.7 \text{ V}$	1, 2, 3	All		20	μA
	I_{IH2}		$V_{IN} = 7.0 \text{ V}$	1, 2, 3	All		0.1	mA
Low level input current	I_{IL}	$V_{CC} = 5.5 \text{ V}$	$V_{IN} = 0.5 \text{ V}$	1, 2, 3	All		-0.6	mA
Short circuit output current	I_{OS}	$V_{CC} = 5.5 \text{ V}, V_{OUT} = 0.0 \text{ V}$		1, 2, 3	All	-60	-150	mA
Off state output current	I_{OZH}	$V_{CC} = 5.5 \text{ V}$	$V_{IN} = 2.7 \text{ V}$	1, 2, 3	All		50	μA
	I_{OZL}	$V_{IH} = 2.0 \text{ V}$	$V_{IN} = 0.5 \text{ V}$	1, 2, 3	All		-50	μA
Power supply current	I_{CCZ}	$V_{CC} = 5.5 \text{ V}$		1, 2, 3	All		100	mA
Functional tests		See 4.3.1c, $V_{CC} = 4.5 \text{ V}, 5.5 \text{ V}$		7, 8	All			
Propagation delay time, CP to Qn	t_{PLH}	$R_L = 500 \Omega$ $C_L = 50 \text{ pF}$ see figure 3	$V_{CC} = 5.0 \text{ V}$	9	All	2.0	9.5	ns
	t_{PHL}		$V_{CC} = 4.5 \text{ V and } 5.5 \text{ V}$	10, 11	All	2.0	10.5	
Output enable time, \overline{OE} to Qn	t_{PZL}		$V_{CC} = 5.0 \text{ V}$	9	All	2.0	10.5	ns
	t_{PZH}		$V_{CC} = 4.5 \text{ V and } 5.5 \text{ V}$	10, 11	All	2.0	13.0	
Output disable time, \overline{OE} to Qn	t_{PLZ}		$V_{CC} = 5.0 \text{ V}$	9	All	1.5	7.0	ns
	t_{PHZ}		$V_{CC} = 4.5 \text{ V and } 5.5 \text{ V}$	10, 11	All	1.0	7.5	

1/ Not more than one output will be shorted at one time and the duration of the short circuit condition shall not exceed one second.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

**SIZE
A**

5962-89438

REVISION LEVEL
D

SHEET
5

Device type	01	
Case outlines	K and L	3
Terminal number	Terminal symbol	
1	OE	NC
2	D0	OE
3	D1	D0
4	D2	D1
5	D3	D2
6	D4	D3
7	D5	D4
8	D6	NC
9	D7	D5
10	D8	D6
11	D9	D7
12	GND	D8
13	CP	D9
14	Q9	GND
15	Q8	NC
16	Q7	CP
17	Q6	Q9
18	Q5	Q8
19	Q4	Q7
20	Q3	Q6
21	Q2	Q5
22	Q1	NC
23	Q0	Q4
24	V _{CC}	Q3
25	---	Q2
26	---	Q1
27	---	Q0
28	---	V _{CC}

FIGURE 1. Terminal connections.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

**SIZE
A**

5962-89438

REVISION LEVEL
D

SHEET
6

Input			Output	Function
\overline{OE}	D _n	CP	Q _n	
H	L		Z	Load
H	H		Z	
H	X	H	Z	Hold
H	X	L	Z	
L	L		L	Data available
L	H		H	
L	X	H	NC	No Change
L	X	L	NC	

H = High level voltage

L = Low level voltage

X = Irrelevant

 = Low to high clock transition

NC = No change

Z = High impedance

FIGURE 2. Truth table.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

SIZE
A

5962-89438

REVISION LEVEL
D

SHEET

7






FIGURE 3. Test circuit and switching waveforms.


**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

**SIZE
A**

5962-89438

REVISION LEVEL
D

SHEET
8



NOTES:

1. C_L includes probe and jig capacitance.
2. All input pulses have the following characteristics: $PRR \leq 1$ MHz, duty cycle = 50%, $t_r = t_f = 2.5$ ns, duty cycle = 50%.
3. When measuring propagation delay times of three-state outputs, switch 1 is open.
4. When measuring pulse widths, $t_r \leq 1$ ns, $t_f \leq 1$ ns.
5. The outputs are measured one at a time with one input transition per measurement.

FIGURE 3. Test circuit and switching waveforms - Continued.

**STANDARD
MICROCIRCUIT DRAWING**
DLA LAND AND MARITIME
COLUMBUS, OHIO 43218-3990

**SIZE
A**

5962-89438

REVISION LEVEL
D

SHEET
9

4. VERIFICATION

4.1 Sampling and inspection. Sampling and inspection procedures shall be in accordance with MIL-PRF-38535, appendix A.

4.2 Screening. Screening shall be in accordance with method 5004 of MIL-STD-883, and shall be conducted on all devices prior to quality conformance inspection. The following additional criteria shall apply:

a. Burn-in test, method 1015 of MIL-STD-883.

(1) Test condition A, B, C or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1015 of MIL-STD-883.

(2) $T_A = +125^{\circ}\text{C}$, minimum.

b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.

TABLE II. Electrical test requirements.

MIL-STD-883 test requirements	Subgroups (in accordance with MIL-STD-883, method 5005, table I)
Interim electrical parameters (method 5004)	---
Final electrical test parameters (method 5004)	1*, 2, 3, 7, 8, 9, 10, 11
Group A test requirements (method 5005)	1, 2, 3, 7, 8, 9, 10, 11
Groups C and D end-point electrical parameters (method 5005)	1, 2, 3

* PDA applies to subgroup 1.

4.3 Quality conformance inspection. Quality conformance inspection shall be in accordance with method 5005 of MIL-STD-883 including groups A, B, C, and D inspections. The following additional criteria shall apply.

4.3.1 Group A inspection.

- a. Tests shall be as specified in table II herein.
- b. Subgroups 4, 5, and 6 in table I, method 5005 of MIL-STD-883 shall be omitted.
- c. Subgroups 7 and 8 shall include verification of the truth table.

STANDARD MICROCIRCUIT DRAWING DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990	SIZE A	5962-89438
	REVISION LEVEL D	

4.3.2 Groups C and D inspections.

- a. End-point electrical parameters shall be as specified in table II herein.
- b. Steady-state life test conditions, method 1005 of MIL-STD-883.
 - (1) Test condition A, B, C or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1005 of MIL-STD-883.
 - (2) $T_A = +125^\circ\text{C}$, minimum.
 - (3) Test duration: 1,000 hours, except as permitted by method 1005 of MIL-STD-883.

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-PRF-38535, appendix A.

6. NOTES

6.1 Intended use. Microcircuits conforming to this drawing are intended for use for Government microcircuit applications (original equipment), design applications, and logistics purposes.

6.2 Replaceability. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.

6.3 Configuration control of SMD's. All proposed changes to existing SMD's will be coordinated with the users of record for the individual documents. This coordination will be accomplished using DD Form 1692, Engineering Change Proposal, or email communication.

6.4 Record of users. Military and industrial users shall inform DLA Land and Maritime when a system application requires configuration control and the applicable SMD to that system. DLA Land and Maritime will maintain a record of users and this list will be used for coordination and distribution of changes to the drawings. Users of drawings covering microelectronics devices (FSC 5962) should contact DLA Land and Maritime-VA, telephone (614) 692-8108.

6.5 Comments. Comments on this drawing should be directed to DLA Land and Maritime-VA, Columbus, Ohio 43218-3990, or telephone (614) 692-0591.

6.6 Approved sources of supply. Approved sources of supply are listed in MIL-HDBK-103 and QML-38535. The vendors listed in MIL-HDBK-103 and QML-38535 have agreed to this drawing and a certificate of compliance (see 3.6 herein) has been submitted to and accepted by DLA Land and Maritime-VA.

STANDARD MICROCIRCUIT DRAWING DLA LAND AND MARITIME COLUMBUS, OHIO 43218-3990	SIZE A	5962-89438
	REVISION LEVEL D	SHEET 11

STANDARD MICROCIRCUIT DRAWING BULLETIN

DATE: 23-01-13

Approved sources of supply for SMD 5962-89438 are listed below for immediate acquisition information only and shall be added to MIL-HDBK-103 and QML-38535 during the next revision. MIL-HDBK-103 and QML-38535 will be revised to include the addition or deletion of sources. The vendors listed below have agreed to this drawing and a certificate of compliance has been submitted to and accepted by DLA Land and Maritime-VA. This information bulletin is superseded by the next dated revision of MIL-HDBK-103 and QML-38535. DLA Land and Maritime maintains an online database of all current sources of supply at <https://landandmaritimeapps.dla.mil/programs/smcr/>.

Standard microcircuit drawing PIN <u>1/</u>	Vendor CAGE number	Vendor similar PIN <u>2/</u>
5962-8943801KA	OC7V7	54F821FMQB
5962-8943801LA	OC7V7	54F821SDMQB
5962-89438013A	OC7V7	54F821LMQB
5962-8943801KA	3V146	54F821/QKA
5962-8943801LA	3V146	54F821/QLA
5962-89438013A	3V146	54F821/Q3A

- 1/ The lead finish shown for each PIN representing a hermetic package is the most readily available from the manufacturer listed for that part. If the desired lead finish is not listed contact the vendor to determine its availability.
- 2/ Caution. Do not use this number for item acquisition. Items acquired to this number may not satisfy the performance requirements of this drawing.

Vendor CAGE number

3V146

OC7V7

Vendor name and address

Rochester Electronics LLC.
16 Malcolm Hoyt Drive
Newburyport, MA 01950

Teledyne e2v, Inc.
765 Sycamore Drive
Milpitas, CA 95035

The information contained herein is disseminated for convenience only and the Government assumes no liability whatsoever for any inaccuracies in the information bulletin.