

UDB 2X35/25 BU - Trunk line branch terminal



3071353

<https://www.phoenixcontact.com/us/products/3071353>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Trunk line branch terminal, nom. voltage: 400 V, nominal current: 125 A, number of connections: 4, number of positions: 1, connection method: Screw connection, 1 level, Rated cross section: 35 mm², cross section: 10 mm² - 35 mm², Screw connection, 2nd level, cross section: 1.5 mm² - 25 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

Your advantages

- The branch terminal is suitable for the simple voltage pick-off of main supply cables
- Conformance with DIN VDE 0603-2/EN 60998-1

Commercial data

Item number	3071353
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BE12
Product key	BE1213
Catalog page	Page 581 (C-1-2019)
GTIN	4046356735988
Weight per piece (including packing)	80.03 g
Weight per piece (excluding packing)	80.03 g
Customs tariff number	85369010
Country of origin	DE

UDB 2X35/25 BU - Trunk line branch terminal



3071353

<https://www.phoenixcontact.com/us/products/3071353>

Technical data

Notes

General	Up to 3 terminal blocks alignable
---------	-----------------------------------

Product properties

Product type	Feed-through terminal block
Number of positions	1
Number of connections	4
Number of rows	1
Potentials	1

Data management status

Article revision	00
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	4.06 W

Connection data

Number of connections per level	4
Nominal cross section	35 mm ²

1 level

Screw thread	M6/M8
Tightening torque	... 4 Nm
Stripping length	25 mm
Connection in acc. with standard	IEC 60998-1
Conductor cross section rigid	10 mm ² ... 35 mm ²
Cross section AWG	6 ... 2 (converted acc. to IEC)
Conductor cross section flexible	10 mm ² ... 25 mm ²
Conductor cross section, flexible [AWG]	6 ... 4 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	10 mm ² ... 25 mm ²
Flexible conductor cross section (ferrule with plastic sleeve)	10 mm ² ... 16 mm ²
Nominal current	125 A
Maximum load current	125 A
Nominal voltage	400 V (max. 1000 V)
Note	Use ferrules for stranded conductors
Nominal cross section	35 mm ²

2nd level

UDB 2X35/25 BU - Trunk line branch terminal



3071353

<https://www.phoenixcontact.com/us/products/3071353>

Stripping length	25 mm
Connection in acc. with standard	IEC 60998-1
Conductor cross section rigid	1.5 mm² ... 25 mm²
Conductor cross-section flexible (ferrule without plastic sleeve)	1.5 mm² ... 16 mm²
Flexible conductor cross section (ferrule with plastic sleeve)	1.5 mm² ... 10 mm²

Dimensions

Width	27 mm
Height	55 mm
Depth on NS 35/7,5	46 mm
Depth on NS 35/15	53.5 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, no longer than 24 h, -60°C to +70°C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60998-1
	IEC 60998-1

Mounting

Mounting type	NS 35/7,5
	NS 35/15
Thread type	()

UDB 2X35/25 BU - Trunk line branch terminal



3071353

<https://www.phoenixcontact.com/us/products/3071353>

Drawings

Circuit diagram



UDB 2X35/25 BU - Trunk line branch terminal



3071353

<https://www.phoenixcontact.com/us/products/3071353>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3071353>



EAC

Approval ID: RU C-DE.A*30.B.01742



VDE Zeichengenehmigung

Approval ID: 40055082

UDB 2X35/25 BU - Trunk line branch terminal



3071353

<https://www.phoenixcontact.com/us/products/3071353>

Classifications

ECLASS

ECLASS-11.0	27141120
ECLASS-13.0	27250119

ETIM

ETIM 9.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UDB 2X35/25 BU - Trunk line branch terminal



3071353

<https://www.phoenixcontact.com/us/products/3071353>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com