



Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Push Button Switch Product Type: **Anti-Vandal Switch**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	With
Actuator Style	Round

Configuration Features

Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Momentary

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage Range	250 VAC

Body Features

Actuator Force	255 g[9 oz]
Case Material	PBT
Product Orientation	Vertical



Actuator Profile	Flush
Bushing Style	Threaded

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver

Housing Features

Process Sealed	Yes
----------------	-----

Industry Standards

IP Rating	IP67
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2213763-1  
AV19 SPM 3A NO LED

TE Part # 3-2213766-7  
AV19 SPL 3A POWER LED BLUE 12V

TE Part # 2213763-5  
AV19 DPM 3A NO LED

TE Part # 2213763-7  
AV19 DPL 3A NO LED

TE Part # 2213767-3  
AV19 SPM 3A MOVE RING LED  
WHITE 24V

Also in the Series | [Alcoswitch AV19](#)

Push Button Switches(472)

Customers Also Bought

TE Part #T4112002051-000  
M12 Field Installable Unshielded

TE Part #324915  
PIDG Ring Tongue Terminals

TE Part #2027395-5  
T9VV1K15-12S

TE Part #1-1674231-1  
2.5MM PITCH BATTERY REC  
ASSEMBLY DIP TYP





TE Part #1674231-1  
2.5MM PITCH HIGH CURRENT BATTE



TE Part #T41514B9L25-002  
RPC-M12L-5FR-1.0-PUR 14AWG GY



TE Part #001-0009  
ANTENNA,2.4/5.5 GHz Dipole



TE Part #2015357-4  
C/A, UMCC/UMCC, 1.37 OD CABLE, 200MM LON

Documents

Product Drawings

AV19 SPM 3A FIXED RING R&B 12V

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2317404-3\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2317404-3\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2317404-3\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch

English

Agency Approvals

UL Report

English