




TE Internal #: 8-321519-1  
Closed End Splice, 12 – 10 AWG Wire Size, .3 – 6 mm² Wire Size,  
3.248 – 13.1 kcmil Wire Size, 3248 – 13100 CMA Wire Size, Copper,  
Purple, Splices  
[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: **Closed End Splice**  
Wire Size: **.3 – 6 mm²**  
Sealable: **No**  
Compatible Insulation Diameter Range: **9.14 mm [ .36 in ]**

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	Closed End Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Product Weight	1.74 g
Primary Product Color	Purple

Contact Features

Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed

Mechanical Attachment



Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	3248 – 13100 CMA
Compatible Insulation Diameter Range	9.14 mm[.36 in]
Terminal Material Thickness	.64 mm[.025 in]
Product Length	31.75 mm[1.25 in]

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 217212-1 PRO-CR ASSY, CES	TE Part # 217212-2 PRO-CR DIE, CES	TE Part # 45219-2 DAHT AMP CLOSED END SPLICES 22-10 ASSY	TE Part # 48208 DAHT CLOSED END SPLICES 22-10 ASSY

Customers Also Bought

TE Part #DT04-2P REC, 2P, GRY, N	TE Part #DT06-2S PLG, 2P, GRY, N	TE Part #W2S Wedgelocks: DEUTSCH DT	TE Part #0460-202-16141 DEUTSCH Solid Contacts

TE Part #282104-1 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING	TE Part #281934-2 SINGLE WIRE SEAL	TE Part #114017-ZZ SEALING PLUG, SIZE 12/16, WHT

Documents

Product Drawings

SPLICE,CE 22-10

English

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_8-321519-1\_Y.3d\_igs.zip



English

Customer View Model

[ENG\\_CVM\\_8-321519-1\\_Y.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_8-321519-1\\_Y.2d\\_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_8-321519-1\\_AM.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-321519-1\\_AM.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-321519-1\\_AM.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English