




SFP28

TE Internal #: 2007538-5

SFP+, Cage Assembly with Integrated Connector, .8mm [.032in]
Centerline, Sealable, Signal, Operating Temperature Range -55 – 105 °C [-67 – 221 °F]

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP+ Stacked Cage Assemblies



Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**

Centerline (Pitch): **.8 mm [.032 in]**

Sealable: **Yes**

Circuit Application: **Signal**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

[All SFP+ Stacked Cage Assemblies \(122\)](#)

Features

Product Type Features

Cage Type	Stacked
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Sealable	Yes
Form Factor	SFP+

Configuration Features

Number of Positions	40
Number of Ports	2
Port Matrix Configuration	2 x 1

Electrical Characteristics

Data Rate (Max)	16 Gb/s
-----------------	---------

Contact Features

Tail Plating Material	Tin
-----------------------	-----



Contact Mating Area Plating Material Thickness	.76 µm
Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel

Termination Features

Termination Post & Tail Length	3 mm[.118 in]
Termination Method to PCB	Through Hole - Press-Fit

Housing Features

Cage Material	Nickel Silver
Centerline (Pitch)	.8 mm[.032 in]

Dimensions

PCB Thickness (Recommended)	1.5 mm[.059 in]
-----------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	SFP+
Heat Sink Compatible	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Elastomeric Gasket

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241)




Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-C11-H50626 SFP+ to SFP+ I/O Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	 TE Part # 2334985-2 SFP28 DIRECT ATTACH CA, 1M, 32AWG
 TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N49011 SFP28 to SFP28 Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG
 TE Part # 4-2821224-5 SFP56 DIRECT ATTACH CA, 3M, 26AWG	 TE Part # 1761394-1 DUST COVER, SFP, GANGED & STACKED	 TE Part # 4-2334985-2 SFP56 DIRECT ATTACH CA, 1M, 32AWG	 TE Part # CAT-C11-H506 SFP+ to SFP+ I/O Cable Assembly: 26 AWG






TE Part # CAT-C11-H5062
SFP+ to SFP+ I/O Cable Assembly: 28 AWG




TE Part # 4-2821222-5
SFP56 DIRECT ATTACH CA, 2M, 30AWG




TE Part # CAT-C11-H5
SFP+ to SFP+ I/O Cable Assembly: 24 AWG



TE Part # 1888901-1
SFP+ EMI Plug



TE Part # 2063048-1
SFP+ 2x4 EXTRACTION TOOL ASSY



TE Part # 2018280-1
KIT, SEATING TOOL, SFP+2x1



TE Part # 2142970-1
CABLE ASSY, MICRO SFP+ TO STD SFP+, 0.5M



TE Part # 2142970-2
CABLE ASSY, MICRO SFP+ TO STD SFP+, 1M

Customers Also Bought



TE Part #1-2007492-5
SFP+ Stacked Cage Assemblies



TE Part #640456-2
PCB Header: Polyester, Vertical, Unshrouded, No Mating Alignment




TE Part #5120534-1
1FHP,64,30A/S,N,C,S10,12,13,15



TE Part #T4140012021-000
M12,REAR MOUNTING,MALE,A CODE,2P



TE Part #2057403-1
IMP100S,R,RA2P10C,LG,39



TE Part #2291634-2
SFP+ 1X1 CAGE ASSY, PF,WITH HEATSINK



TE Part #9522364001
CGPT-19/9.5-0-FSP

Documents

Product Drawings

SFP+assy 2x1 Gasket 4 LP Sn

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2007538-5_E1.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2007538-5_E1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2007538-5_E1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1773408-1 Pluggable Input/Output Solutions catalog - SFP+ section](#)

English

[SFP+ Product Family: Cages, Connectors, Cable Assemblies 4-1773449-5](#)

English

[4-1773455-3 - Quick Reference Guide SFP+ Solutions](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English