




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **14**
Centerline (Pitch): **2.54 mm [.1 in]**
Row-to-Row Spacing: **2.54 mm [.1 in]**
Number of Rows: **2**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	14
Number of Rows	2

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Wire Contact Termination Area Plating Thickness	.127 μm[5 μin]
Wire Contact Termination Area Plating Material	Gold Flash
	30 μin



Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS	 TE Part # 5088450-3 PULL LOOP, CUT LENGTH .64 IN	 TE Part # 104128-2 014 LOPRO HDR SP 30DP LATCH	 TE Part # 1761606-5 IDC LOW PRO HDR 14P VERT LG LA
 TE Part # 2-1761603-5 IDC LOW PRO HDR 14P VERT BLUE	 TE Part # 5103309-2 A/L LOW PRO HDR 14P VERT BLACK	 TE Part # 2-1761609-5 IDC LOW PRO HDR 14P RA SHT LAT BLUE	 TE Part # 5103310-2 A/L LOW PRO HDR 14P RA BLACK
 TE Part # 1761607-5 IDC LOW PRO HDR 14P RA LG LAT BLK	 TE Part # 1-111446-5 14 UNIV I/O, NO EARS, LEAD FREE	 TE Part # 2-1761606-5 IDC LOW PRO HDR 14P VERT LG LA	 TE Part # 5103308-2 A/L LOW PRO HDR 14P VERT BLACK
 TE Part # 2-1761607-5 IDC LOW PRO HDR 14P RA LG LAT	 TE Part # 1761608-5 IDC LOW PRO HDR 14P VERT SHT L	 TE Part # 2-1761608-5 IDC LOW PRO HDR 14P VERT SHT L	 TE Part # 1761609-5 IDC LOW PRO HDR 14P RA SHT LAT



TE Part # 5103311-2
A/L LOW PRO HDR 14P RA BLACK

TE Part # 5104338-2
A/L LOW PRO HDR 14P VERT HT

TE Part # 1-111504-5
014 UNIV I/O 30DP NO EARS LTCH

TE Part # 1761681-5
IDC LOW PRO HDR 14P VERT HT BLACK

Customers Also Bought

TE Part #5499922-2
A/L UNIV HDR 14P VERT LG LAT

TE Part #1658610-3
15 POS HDF RCPT, MS, LEAD FREE

TE Part #2-1658527-2
622-1441LF=FSKT IDC S 14 30AU

TE Part #3-2213766-7
AV19 SPL 3A POWER LED BLUE 12V

TE Part #5-1437624-1
PKES60B1/8=KNOB

TE Part #2118710-2
1 PC STD SHIELD, CRS-38.10X25.40X6.00MM

TE Part #254539-E
SMCQ 40 M AB VV 8-03 CL * H007 137 E005

TE Part #254590-E
SMCQ 40 M AB VV 8-13 CL * H007 137 E005

TE Part #354065-E
SMCB 40 F AB VV 7-03 CL * H007 137 E002

Documents

Product Drawings
622-1430LF FEM SOCKT,LEAD FREE
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1658527-5_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1658527-5_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1658527-5_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ribbon Cable Interconnect Solutions](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English