



12		11		10		9		8		7		
LOOSE PIECE BOX		TAPE MOUNTED PARTS		STUD SIZE	ØS	ØW ±.012/0.30	L MAX	C MIN	T REF	H ±.02/0.5		
MAT'L NO.	ENG NO.	MAT'L NO.	ENG NO.									
190710132	D-650-06X	190710133	D-650-06XT	6	.146/3.71	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18		
190710134	D-650-08X	190710135	D-650-08XT	8	.173/4.39	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18		
190710136	D-650-10X	190710139	D-650-10XT	10	.198/5.03	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18		
190710140	D-650-14X	190710143	D-650-14XT	1/4	.265/6.73	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18		
190710144	D-650-56X	190710145	D-650-56XT	5/16	.328/8.33	.468/11.89	1.31/33.3	.363/9.22	.045/1.14	1.070/27.18		
190710146	D-651-10X	-	-	10	.198/5.03	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	-		
190710148	D-651-14X	190710149	D-651-14XT	1/4	.265/6.73	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	1.070/27.18		
190710153	D-651-56X	190710155	D-651-56XT	5/16	.328/8.33	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	1.070/27.18		
190710150	D-651-38X	190710152	D-651-38XT	3/8	.390/9.91	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	1.070/27.18		
190710156	D-651-76X	-	-	7/16	.453/11.51	.583/14.81	1.43/36.3	.428/10.87	.045/1.14	-		
190710158	D-652-10X	-	-	10	.198/5.03	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	-		
190710161	D-652-14X	-	-	1/4	.265/6.73	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	-		
190710163	D-652-56X	-	-	5/16	.328/8.33	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	-		
190710162	D-652-38X	-	-	3/8	.390/9.91	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	-		
190710166	D-652-76X	-	-	7/16	.453/11.51	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	-		
190710334	D-652-12X	190710160	D-652-12XT	1/2	.515/13.08	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	1.400/35.56		
190710164	D-652-58X	-	-	5/8	.656/16.66	.810/20.57	1.73/43.9	.611/15.52	.050/1.27	-		
190710172	D-653-56X	-	-	5/16	.328/8.33	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-		
190710171	D-653-38X	-	-	3/8	.390/9.91	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-		
190710174	D-653-76X	-	-	7/16	.453/11.51	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-		
190710168	D-653-12X	-	-	1/2	.515/13.08	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-		
190710173	D-653-58X	-	-	5/8	.656/16.66	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-		
190710170	D-653-34X	-	-	3/4	.781/19.84	1.125/28.58	2.28/57.9	.986/25.04	.050/1.27	-		
190710176	D-656-06X	190710177	D-656-06XT	6	.146/3.71	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18		
190710178	D-656-08X	190710179	D-656-08XT	8	.173/4.39	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18		
190710180	D-656-10X	190710181	D-656-10XT	10	.198/5.03	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18		
190710182	D-656-14X	190710184	D-656-14XT	1/4	.265/6.73	.374/9.50	1.27/32.3	.363/9.22	.045/1.14	1.070/27.18		



- NOTES:
- MATERIALS:
TERMINAL: TIN-PLATED COPPER
INSULATION: RED PVC
 - PARTS ARE RoHS COMPLIANT.
 - MWID = MAXIMUM WIRE INSULATION DIAMETER.



PARTS ON TAPE
(DOUBLE SPACED)

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
= 0 = 0 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: REDRAWN TO NX, WAS .33				molex				
	INCH/MM		1:1										
	DIVISIONAL SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 754508 DRWN: DEANNM1 2023/06/22 CHK'D: JMACNEIL 2023/06/26 APPR: JMACNEIL 2023/06/26				RING TONGUE TERMINALS 8 AWG INSULKRIMP			
		MM		INCH									
4 PLACES		±		±									
3 PLACES		±		± 0.005									
2 PLACES		±	0.13	± 0.01									
1 PLACE		±	0.25	± 0.02	PRODUCT CUSTOMER DRAWING								
0 PLACES		±		±					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
ANGULAR TOL ± 0.5 °				SD-19071-002					PSD	001	C1		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER	SHEET NUMBER		
						C-SIZE	19071			GENERAL MARKET	1 OF 1		