





REV. 1 8/15/97

COIL:

RESISTANCE 5000 OHMS ± 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 2.8 mA

MUST RELEASE

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 15 g's

SHOCK 50 g's 11 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 15 MS MAX.

RELEASE TIME 10 MS MAX.

CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 2A 28 VDC
RESISTIVE 100,000 OPERATIONS

DR. R.B. 8/13/97 CK. 3/15/2005

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD.

CUST NO.

TYPE 'SF' RELAY

SF5205W00