


LTCC High Temperature Inductors 0.30x0.30 inch Size

NASCENTTechnology, Inc. has developed a series of high temperature, RoHS compliant inductors using low temperature co-fired ceramic (LTCC) ferrite usable to 300°C that feature low profile, rugged packaging, and self shielding characteristics. See individual data sheets for part dimensions.



Electrical Parameters at 25 °C unless otherwise noted

Part No.	No Load Inductance [†] μH	100 mA Inductance μH	100 mA Tolerance	Nominal DC Resistance ohms	Rated Current ^{††} mA	Saturation Current* mA
85022	10	5.9	20%	0.12		250
85024	12	10	20%	0.20		250
85027	21	19	20%	0.30		250
85028	51	30	20%	0.60		250
85032	48	43	25%	1.00		250
85031	88	47	20%	1.20		250
85035	86	67	20%	1.90		250
85036	100	85	25%	1.35		250
85038	175	125	25%	2.43		250

[†] Tolerance for no load inductance is ±25 %

^{††} Current will cause a 35 °C temperature rise over ambient (measured 20 to 55 °C)

* Saturation Current is the current that results in a 35% decrease in inductance over the 100 mA Inductance.
Thickness varies by part; the range is 0.032-0.100 in [0.8-2.54 mm]

Common termination options (please add option to the end of the part number when inquiring):

- A0 Thick film AgPt with side terminations, solderable
- C0 Thick film Au, Au wirebonding
- D0 Au over Ni, solderable
- D1 Au over Ni, Al wirebonding

For additional information, contact: Daryl Schofield, General Manager
Phone : 605-882-8513, Fax : 605-884-2450, E-mail : dschofield@nascenttechnology.com
NASCENTTechnology Manufacturing, Inc. 1404 9th Ave. SW, Watertown, SD 57201
www.nascenttechnology.com