



Connectors > Power Connectors > Circular Power > Circular Power Connectors > Connectors with Posted Pin Contacts, CPC Series 1



Connector Product Type: **Connector Assembly**
Operating Voltage: **250 VDC**
Connector System: **Wire-to-Board, Wire-to-Panel**
Number of Positions: **16**
Sealable: **No**

[All Connectors with Posted Pin Contacts, CPC Series 1 \(39\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board, Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Number of Positions	16
Number of Power Positions	0
Number of Signal Positions	16

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------



Contact Features

Reverse Gender	No
Contact Type	Pin

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Panel Mount Feature Type	Flange with Threaded Inserts
Mating Retention Type	Threaded Coupling
Polarization Code	A
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Housing Features

Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	17

Dimensions

Assembly Length	40 mm[1.575 in]
-----------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	24
Packaging Method	Tray



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 207299-3
FLANGE PLUG MOUNT CPC



TE Part # CAT-AM71-C83998B
CPC Cable Clamps



TE Part # 207241-1
CABLE BOOT, SZ 17, CPC



TE Part # 207387-1
CABLE GRIP, SZ 17, CPC



TE Part # 207387-2
CABLE GRIP,SZ 17,CPC

TE Part # 4-2407269-4
CAP, CPC, SIZE 17 RECP, YELLOW

TE Part # 4-2407269-3
CAP, CPC, SIZE 17 RECP, RED

TE Part # 4-2407269-2
CAP, CPC, SIZE 17 RECP, BLACK

TE Part # 4-2407269-1
CAP, CPC, SIZE 17 RECP, ORANGE

TE Part # 1-207303-6
CPC RECPT ASSM SIZE 17-16

Also in the Series | AMP CPC

Circular Power Connectors(458)

Connector Backshells(1)

Connector Caps & Covers(19)

Connector Contacts(6)

Connector Hardware(12)

Connector Seals & Cavity Plugs(36)




Connector Strain Relief(60)

Insertion & Extraction Tools(1)

Sealing Sleeves(2)

Customers Also Bought



 TE Part #2102061-2 Mezalok, Socket, 114 p, 10 mm, 50 Au, LF	 TE Part #F71606-000 WP-229064-10-9	 TE Part #2000713-2 RA Keyed Guide Mod. Vita 46, Machined	 TE Part #2040002-1 MICRO USB, TYPE B
 TE Part #6-66460-2 PIN,.062 DIA,.025 SQ POST,LP	 TE Part #796638-8 8POS 5.08MM CE R/A HDR,TRM BLK	 TE Part #7-1879211-9 CPF 0402 11K8 0.1% 25PPM 5K RL	 TE Part #1-208223-1 CPC RCPT ASSEMBLY SIZE 13-9
 TE Part #2311586-4 AMPL REC, HD22, R/A, 15P, THREADED, BLUE	 TE Part #4-1827253-8 .5FHP05H,220,S,GIG,08/Sn,TR,NSYes		

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-207303-4_AE.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-207303-4_AE.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-207303-4_AE.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications



Connector, Circular Plastic

English

Product Specification

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English