

COAXIAL CONNECTOR, 7/16, 50 Ohm, Straight panel cable jack (female), flange mount

25_716-50-0-2/003_-

Properties

- Rugged connection for COM-Applications
- For medium and high power connection
- Applicable in frequencies up to 7.5 GHz
- IEC Standardized



Product configuration

Interface type	Gender	Standard
7/16	jack	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data

Piece parts	Material	Plating
Centre contact	Bronze / Brass	Silver Plating
Outer conductor	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	7.5 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 1 GHz	24.9 dB	1.12
1 GHz ... 2.5 GHz	20 dB	1.22
2.5 GHz ... 5 GHz	14 dB	1.5

Mechanical data

Weight	0.1239 kg
Mating cycles	500

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, 7/16, 50 Ohm, Straight panel cable jack (female), flange mount

25_716-50-0-2/003_-

Ordering Information Table		
Item number	Item description	Packaging type
22641434	25_716-50-0-2/003_-E	Single
Additional Information		
Only as assembly	No	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2527 / Date of publication: 25.11.2023 / uncontrolled copy