

# EV-T2M3S-E-LOCK12V - Locking



1624129

<https://www.phoenixcontact.com/us/products/1624129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CHARX connect modular, Locking, Accessories, for attaching to infrastructure charging sockets, Type 2, GB/T, IEC 61851-1, Single wires, length: 0.5 m, locking actuator: 12 V, 4-pos.



## Product description

Locking actuator with 12 V power supply for infrastructure charging sockets

## Your advantages

- Integrated interlock during charging
- Manual emergency release of the locking actuator
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Uniform, space-saving installation space

## Commercial data

Item number	1624129
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBAFC
GTIN	4055626239880
Weight per piece (including packing)	152 g
Weight per piece (excluding packing)	95 g
Customs tariff number	85011099
Country of origin	DE

# EV-T2M3S-E-LOCK12V - Locking



1624129

<https://www.phoenixcontact.com/us/products/1624129>

## Technical data

### Product properties

Product type	Locking actuator
Product family	CHARX connect modular
Application	for attaching to infrastructure charging sockets
Type	Accessories
Charging standard	Type 2
	GB/T
Charging mode	Mode 2, 3, 4

### Electrical properties

#### Locking actuator

Operating voltage	12 V
Note number of positions	4-pos.
Position of the locking actuator	any

#### Locking actuator

Operating voltage	12 V
Note number of positions	4-pos.
Position of the locking actuator	any
Possible power supply range at the motor	9 V ... 16 V
Maximum voltage for locking detection	30 V
Typical motor current for locking	0.2 A
Reverse current of the motor	max. 1 A
Max. dwell time with reverse current	1000 ms
Recommended adaptation time	600 ms
Pause time after entry or exit path	3 s
Service life insertion cycles	> 10000 load cycles
Lock recognition	available
Mechanical emergency release	available
Ambient temperature (operation)	-30 °C ... 50 °C

### Material specifications

Color (Locking)	black (9005)
-----------------	--------------

### Cable/line

Cable length	0.5 m
Cable type	Single wires
Cable structure	4 x 0.5 mm <sup>2</sup>
Single wire, material	PVC
Single wire, color	BU/RD
	BU/GN

# EV-T2M3S-E-LOCK12V - Locking



1624129

<https://www.phoenixcontact.com/us/products/1624129>

	BU/YE
	BU/BN
External cable diameter	1.60 mm $\pm$ 0.20 mm
Cable resistance	$\leq$ 37.1 $\Omega$ /m

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-30 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	5000 m (above sea level)

## Standards and regulations

### Standards

Standards/regulations	IEC 61851-1
-----------------------	-------------

## Mounting

Thread type	()
-------------	----


# EV-T2M3S-E-LOCK12V - Locking

1624129

<https://www.phoenixcontact.com/us/products/1624129>

## Drawings

Schematic diagram




Lever positions for emergency release


EV-T2M3S-E-LOCK12V - Locking




1624129  
<https://www.phoenixcontact.com/us/products/1624129>



Detection of the Infrastructure Plug




Block diagram of the locking actuator



Locking states of the locking actuator

Schematic diagram



Lever positions for emergency release

# EV-T2M3S-E-LOCK12V - Locking



1624129

<https://www.phoenixcontact.com/us/products/1624129>

## Classifications

### ECLASS

ECLASS-11.0	27144792
ECLASS-12.0	27144792
ECLASS-13.0	27144792

### ETIM

ETIM 9.0	EC002884
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# EV-T2M3S-E-LOCK12V - Locking



1624129

<https://www.phoenixcontact.com/us/products/1624129>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c86cccb9-5c52-42c7-9d6e-afffab27783a



# EV-T2M3S-E-LOCK12V - Locking

1624129

<https://www.phoenixcontact.com/us/products/1624129>



## Accessories

### EV-T2M3S-E-LOCK-HOLDER - Holder

1065832

<https://www.phoenixcontact.com/us/products/1065832>

CHARX connect modular, Holder, Accessories, for mounting the 4-pole locking actuator on infrastructure charging sockets, Type 2, GB/T, IEC 61851-1



---

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)