



Printed: May 16, 2009



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



mat'l code				--		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com			
lfr	ecn no.	dr	date	linear	0.X $\pm$ 0.3		COPY			title METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT					
CA					0.XX $\pm$ 0.13		projection								
					.XXX $\pm$.051										
				angles	0° $\pm$ 2°										
				dr	T.BRUNGARD 11/19/99				product family				METRAL		code
				enrg	M.STRAWSER 11/19/99				size		dwg no		213		
				chr	M.STRAWSER 11/19/99				A		70299		sheet		
				appd	M.STRAWSER 02/29/00		scale 1:1							2	
sheet index		revision sheet													

cage code 22526

Pro/E

PDM: Rev:CA

STATUS: Released

Printed: May 16, 2009



A

B

1 | 2

3 |

4

PRODUCT NUMBER	DESCRIPTION	PLATING IN PRESS FIT TAIL AREA	PERFORMANCE LEVEL OF PLATING IN CONTACT AREA
70299-AYY	STANDARD	TIN-LEAD	TELCORDIA CO (SEE NOTE 9)
70299-NIYY	STANDARD	TIN-LEAD	TELCORDIA CO (NXT)
70299-N5YY	STANDARD	TIN-LEAD	TECORDIA UE (NXT)
70299-IYY	STANDARD	TIN-LEAD	TELCORDIA CO
70299-2YY	STANDARD	TIN-LEAD	TELECOM CLASS
70299-3YY	STANDARD	TIN-LEAD	IEC CLASS I
70299-5YY	STANDARD	TIN-LEAD	TELCORDIA UE
70299-9YY	STANDARD	TIN-LEAD	TELCORDIA CO
70299-NIYYLF	LEAD FREE	TIN	TELCORDIA CO (NXT), IEC CLASS I, SEE NOTES 9 AND 10
70299-N5YYLF	LEAD FREE	TIN	TECORDIA UE (NXT) SEE NOTES 9 AND 10
70299-IYYLF	LEAD FREE	TIN	TELCORDIA CO, IEC CLASS I, SEE NOTES 9 AND 10
70299-2YYLF	LEAD FREE	TIN	TELECOM CLASS, SEE NOTES 9 AND 10
70299-5YYLF	LEAD FREE	TIN	TELCORDIA UE, SEE NOTES 9 AND 10

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON: PRESS-FIT TAIL AREA SEE PRODUCT.
NUMBER TABLE, PLATING ON CONTACT AREA CONFORMS
TO PERFORMANCE LEVEL SHOWN IN TABLE ON SHEET3.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF
- PRODUCT SPECIFICATION:
GS-12-180
APPLICATION SPECIFICATION:
BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH QUALIFIED TOOL.
- A PLATING HAS Au FLASH IN PRESS FIT AREA (LEAD FREE)
- THE PRODUCTS WHERE THE PART NUMBERS ENDS IN
LF MEET THE EUROPEAN UNION DIRECTIVE AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-12-008.
- ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS
CONTAINING 70299-NI--- OR 70299-N5--- WILL WITHSTAND
EXPOSURE TO 260 DEGREES C FOR 60 SECONDS IN A
CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN
PART NUMBERS 70299-NI--- AND 70299-N5--- WILL
NOT WITHSTAND REFLOW AND THE Au CONTACT SURFACE
OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140
DEGREES C FOR NO LONGER THAN 15 SECONDS IN A WAVE
SOLDER APPLICATION.

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com		
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY				
CA					0.XX ±0.13	projection				
					.XXX ±.051					
					0° ±2°					
				angles	0° ±2°					
				dr	T.BRUNGARD	11/19/99	MM		product family METRAL code	
				enrg	M.STRAWSE	11/19/99	A		size dwg no	
				chr	M.STRAWSE	11/19/99	scale		70299	
				appd	M.STRAWSE	02/29/00	1:1		sheet 3	
sheet index		revision sheet							cage code 22526	

A

B

Pro/E

3 |

4



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X01 AND 70299-X01LF	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X02 AND 70299-X02LF	D	-	1	-	-	-	1	-	1	-	-	-	1	-	1	1	1	-	1	-	1	-	1	-	1
	C	1	-	-	-	1	-	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	B	-	1	-	-	-	1	-	1	-	-	-	1	-	1	1	1	-	1	-	1	-	1	-	1
	A	1	-	1	-	1	-	-	-	1	-	1	-	3	-	3	-	1	-	1	-	1	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X03 AND 70299-X03LF	D	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	C	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X04 AND 70299-X04LF	D	7	5	5	5	5	5	5	5	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X05 AND 70299-X05LF	D	7	5	5	5	5	5	5	5	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	8	8	8	8	8	8	8	7	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X06 AND 70299-X06LF	D	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5
	C	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5
	B	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5
	A	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X07 AND 70299-X07LF	D	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	20	20	20	5	20	2
	C	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	20	20	20	5	20	2
	B	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	20	20	20	5	20	2
	A	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	20	20	20	5	20	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X08 AND 70299-X08LF	D	7	7	5	5	5	5	5	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5	7	7
	C	7	7	5	5	5	5	5	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5	7	7
	B	7	7	5	5	5	5	5	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5	7	7
	A	7	7	5	5	5	5	5	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X09 AND 70299-X09LF	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X10 AND 70299-X10LF	D	-	1	-	1	-	1	-	1	-	-	-	1	-	1	1	-	1	-	1	-	1	-	1	-
	C	1	-	-	1	1	-	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	B	-	1	-	-	-	1	-	1	-	-	-	1	-	1	1	-	1	-	1	-	1	-	1	-
	A	1	-	1	-	1	-	-	1	-	1	-	3	-	3	-	1	-	1	-	1	-	1	-	1

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
CA				linear	0.XX ±0.13	projection		title	
				angles	.XXX ±.051			METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99			product family	
				enrg	M.STRAWSE 11/19/99	MM		METRAL	
				chr	M.STRAWSE 11/19/99	scale		code	
				appd	M.STRAWSE 02/29/00	1:1		213	
sheet	revision							sheet	
index	sheet							4	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X11 AND 70299-X11LF	D	2	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X12 AND 70299-X12LF	D	3	1	1	1	1	1	1	1	2	2	2	2	2	2	3	3	3	3	2	2	2	2	2	2
	C	3	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	3	2	2	2	2	2	3	3	3	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X13 AND 70299-X13LF	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	5	5	5	5	5	5	5	5
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	5	5	5	5	5	5	5	5
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	5	5	5	5	5	5	5	5
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X14 AND 70299-X14LF	D	6	5	5	5	5	5	5	6	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X15 AND 70299-X15LF	D	7	5	5	5	5	5	5	5	6	6	6	6	6	6	7	7	7	7	6	6	6	6	6	6
	C	7	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	7	6	6	6	6	6	7	7	7	7	7	7	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X16 AND 70299-X16LF	D	6	5	5	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X17 AND 70299-X17LF	D	5	5	5	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	7	7	7	7	7	7	7	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X18 AND 70299-X18LF	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	5	5	5	5	5	5	5	5
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X19 AND 70299-X19LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	3
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	3
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	3
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	3

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X20 AND 70299-X20LF	D	4	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2
	C	2	2	2	2	2	2	2	2	1	1	1	1	2	2	2	2	2	2	2	2	2	1	2	2
	B	2	2	2	2	2	2	2	2	1	1	1	1	2	2	2	2	2	2	2	2	2	1	2	2
	A	2	2	2	2	2	2	2	2	1	1	1	1	2	2	2	2	2	2	2	2	2	1	2	2

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
CA				linear	0.XX ±0.13	projection		title	
				angles	.XXX ±.051			METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99			product family	
				engr	M.STRAWER 11/19/99	MM		METRAL	
				chr	M.STRAWER 11/19/99	scale		code	
				appd	M.STRAWER 02/29/00	1:1		213	
sheet index	revision	sheet						sheet	
								5</	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X21 AND 70299-X21LF	D	4	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	4	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X22 AND 70299-X22LF	D	4	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X23 AND 70299-X23LF	D	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5
	C	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	5
	A	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X24 AND 70299-X24LF	D	19	19	1	3	3	4	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19
	C	19	19	1	3	3	4	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19
	B	19	19	1	3	3	4	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19
	A	19	19	1	3	3	4	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
70299-X25 AND 70299-X25LF	D	19	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19
	C	19	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19
	B	19	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19
	A	19	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X26 AND 70299-X26LF	D	2	2	2	2	2	2	3	4	2	2	2	2	3	2	4	2	2	3	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	1	1	1
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	1	1	1
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X27 AND 70299-X27LF	D	2	2	2	2	2	2	3	4	2	2	2	2	3	2	4	2	2	3	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	4	4	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X28 AND 70299-X28LF	D	2	2	2	2	2	2	3	4	2	2	2	2	3	2	4	2	2	3	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X29 AND 70299-X29LF	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	5	5	5	5	5	5	5
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	5	5	5	5	5	5	5
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X30 AND 70299-X30LF	D	4	4	1	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		FCJ www.fcjconnect.com		
lfr	ecn no.	dr	date	linear	0.X ±0.3		COPY		projection 	title		
CA					0.XX ±0.13					METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT		
					.XXX ±.051							
					0° ±°							
				angles								
				dr	T.BRUNGARD	11/19/99						
				engr	M.STRAWSE	11/19/99						
				chr	M.STRAWSE	11/19/99						



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X31 AND 70299-X31LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X32 AND 70299-X32LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X33 AND 70299-X33LF	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	4	4	4	4	4	3	4	3	3	3	3	-	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X34 AND 70299-X34LF	D	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	3	3	3	3	3	3	3
	C	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	3	3	3	3	3	3	3
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X35 AND 70299-X35LF	D	6	6	6	6	6	6	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	C	6	6	6	6	6	6	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	B	6	6	6	6	6	6	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	A	6	6	7	7	6	6	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X36 AND 70299-X36LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	2	2	2	2	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	2	2	3	3	2	4	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X37 AND 70299-X37LF	D	2	2	2	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X38 AND 70299-X38LF	D	5	5	5	5	5	5	5	5	5	5	5	5	5	5	7	5	7	7	5	7	5	5	5	5
	C	5	5	5	5	5	5	5	5	5	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	7	5	5	5
	A	5	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	7	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X39 AND 70299-X39LF	D	4	3	1	1	1	1	1	1	1	1	1	4	-	-	-	1	1	2	1	1	-	1	-	4
	C	4	1	1	1	1	1	1	1	1	1	1	-	-	-	1	2	3	1	1	-	1	-	4	
	B	4	2	1	1	1	1	1	1	1	1	1	-	-	-	-	-	1	1	1	-	1	-	4	
	A	4	3	1	1	1	1	1	1	1	1	1	-	-	-	1	-	-	1	1	1	-	1	-	4

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X40 AND 70299-X40LF	D	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	21	11	9	9	9	9
	C	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	21	11	11	9	9	9
	B	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	21	11	11	9	9	9
	A	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	9	21	9	21	9	11	1

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
CA				linear	0.XX ±0.13	projection		title	
				angles	.XXX ±.051			METRAL SIGNAL HEADER	
				dr	T.BRUNGARD 11/19/99			4 MOD, 4 ROW PRESS-FIT	
				engr	M.STRAWSE 11/19/99	MM		product family	
				chr	M.STRAWSE 11/19/99	scale		METRAL	
				appd	M.STRAWSE 02/29/00	1:1		code	
sheet	revision							213	
index	sheet							sheet	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X41 AND 70299-X41LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	3	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	3	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X42 AND 70299-X42LF	D	4	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	3
	C	4	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	3
	B	4	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	3
	A	4	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X43 AND 70299-X43LF	D	3	3	3	3	3	3	4	4	4	4	4	4	1	1	1	1	1	1	1	1	1	1	1	1
	C	3	3	3	3	3	3	4	4	4	4	4	4	1	1	1	1	1	1	1	1	1	1	1	1
	B	3	3	3	3	3	3	4	4	4	4	4	4	1	1	1	1	1	1	1	1	1	1	1	1
	A	3	3	3	3	3	3	4	4	4	4	4	4	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X44 AND 70299-X44LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X45 AND 70299-X45LF	D	3	3	3	3	3	3	4	4	4	4	4	4	5	5	5	5	5	5	5	5	5	5	5	5
	C	3	3	3	3	3	3	4	4	4	4	4	4	5	5	5	5	5	5	5	5	5	5	5	5
	B	3	3	3	3	3	3	4	4	4	4	4	4	5	5	5	5	5	5	5	5	5	5	5	5
	A	3	3	3	3	3	3	4	4	4	4	4	4	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X46 AND 70299-X46LF	D	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	1	1	1	1	1
	C	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	1	1	1	1	1
	B	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	1	1	1	1	1
	A	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X47 AND 70299-X47LF	D	3	3	3	3	3	4	4	4	4	4	4	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	3	3	3	3	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	3	3	3	3	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	3	3	3	3	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X48 AND 70299-X48LF	D	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5	5	5	5	5	5	5
	C	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5	5	5	5	5	5	5
	B	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5	5	5	5	5	5	5
	A	1	1	1	1	1	1	1	1	1	1	1	1	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X49 AND 70299-X49LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	2	2	2	2	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	2	2	2	2	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X50 AND 70299-X50LF	D	6	6	6	6	6	8	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	C	6	6	6	6	6	6	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	B	6	6	6	6	6	6	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	A	6	6	7	7	6	6	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3		COPY		projection 	title	
CA					0.XX ±0.13					METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT	
					.XXX ±.051						
				angles	0° ±°				MM scale 1:1	product family	
				dr	T.BRUNGARD 11/19/99					METRAL	
				engr	M.STRAWSE 11/19/99					code	
				chr	M.STRAWSE 11/19/99				size	dwg no	
				appd	M.STRAWSE 02/29/00					70299	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X51 AND 70299-X51LF	D	19	2	3	2	3	3	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	C	19	3	3	3	3	3	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	B	19	3	3	3	3	3	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7
	A	19	3	1	3	3	3	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X52 AND 70299-X52LF	D	19	2	3	2	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	B	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	19	3	1	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X53 AND 70299-X53LF	D	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	3	3	3
	C	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	3	3	3
	B	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	3	3	3
	A	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
70299-X54 AND 70299-X54LF	D	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	1	19
	C	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	2	19
	B	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19
	A	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X55 AND 70299-X55LF	D	19	3	3	3	3	3	3	3	3	3	1	19	7	7	7	7	7	7	7	7	7	7	7	7
	C	19	3	3	3	3	3	3	3	3	3	2	19	7	7	7	7	7	7	7	7	7	7	7	7
	B	19	3	3	3	3	3	3	3	3	3	3	19	7	7	7	7	7	7	7	7	7	7	7	7
	A	19	3	3	3	3	3	3	3	3	3	3	19	7	7	7	7	7	7	7	7	7	7	7	7


METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X56 AND 70299-X56LF	D	19	3	3	3	3	3	7	7	7	7	7	7	3	3	3	3	3	3	3	3	3	3	3	3
	C	19	3	3	2	3	3	7	7	7	7	7	7	3	3	3	3	3	3	3	3	3	3	3	3
	B	19	3	3	3	3	3	7	7	7	7	7	7	3	3	3	3	3	3	3	3	3	3	3	3
	A	19	3	1	3	3	3	7	7	7	7	7	7	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X57 AND 70299-X57LF	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	7	7	7	7	7	7
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	7	7	7	7	7	7
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	7	7	7	7	7	7
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X58 AND 70299-X58LF	D	7	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5	5	5	5
	C	7	5	7	5	7	5	5	5	5	5	5	5	5	7	7	7	7	7	7	7	7	7	7	
	B	7	7	7	7	5	5	5	5	5	7	7	7	7	7	7	7	7	7	7	7	7	7	7	
	A	5	5	5	5	5	5	7	7	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X59 AND 70299-X59LF	D	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	C	7	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X60 AND 70299-X60LF	D	7	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5	5	5	5
	C	7	5	7	5	5	5	5	5	5	5	5	5	5	7	7	7	7	7	7	7	7	7	7	
	B	7	7	7	7	5	5	5	5	5	7	7	7	7	7	7	7	7	7	7	7	7	7	7	
	A	5	5	5	5	5	7	7	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com		
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		projection				
CA				linear	0.XX ±0.13					title		
				angles	.XXX ±.051					METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT		
				dr	T.BRUNGARD	11/19/99			product family		METRAL	code
				enrg	M.STRAWSE	11/19/99			size		dwg no	213
				chr	M.STRAWSE	11/19/99			A		70299	sheet



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X61 AND 70299-X61LF	D	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	C	7	7	7	7	7	7	7	7	7	7	7	5	5	5	5	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X62 AND 70299-X62LF	D	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5
	C	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	5	5	5	5
	B	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	7	7	5	5	5
	A	5	5	5	5	5	7	5	5	5	5	5	7	5	5	5	5	5	7	5	7	7	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X63 AND 70299-X63LF	D	7	6	6	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	6	6	7	7
	C	7	6	6	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	6	6	7	7
	B	7	6	6	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	6	6	7	7
	A	7	6	6	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	6	6	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X64 AND 70299-X64LF	D	3	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	3	3
	C	3	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	3	3
	B	3	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	3	3
	A	3	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X65 AND 70299-X65LF	D	1	1	-	1	1	-	1	1	-	-	1	1	-	1	1	-	1	1	1	1	1	1	1	1
	C	1	1	-	1	1	-	1	1	-	-	1	1	-	1	1	-	1	1	1	1	1	1	1	1
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X66 AND 70299-X66LF	D	1	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	-	1	3	3	3	3	3	1	3	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X67 AND 70299-X67LF	D	19	2	3	2	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	B	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	19	3	1	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X68 AND 70299-X68LF	D	1	-	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	B	1	1	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	A	1	1	1	1	1	-	1	3	3	3	3	3	1	3	1	1	1	1	-	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X69 AND 70299-X69LF	D	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X70 AND 70299-X70LF	D	2	2	2	2	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	C	2	2	2	2	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	B	2	2	2	2	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	A	2	2	2	2	2	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		projection			
CA				linear	0.XX ±0.13					title	
				angles	.XXX ±.051					METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99			product family		METRAL	
				enrg	M.STRAWSE 11/19/99			size		dwg no	
				chr	M.STRAWSE 11/19/99			A		70299	
				appd	M.STRAWSE 02/29/00			sheet		213	
sheet index		revision sheet								sheet 10	

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X72 AND 70299-X72LF	D	1	1	2	3	4	5	6	1	1	1	1	1	1	1	1	1	1	3	2	2	2	2	2	3
	C	1	1	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	2	2	2	2	2	3
	B	1	1	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	2	2	2	2	2	3
	A	1	1	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	2	2	2	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X73 AND 70299-X73LF	D	2	2	2	2	2	3	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	3
	C	2	2	2	2	2	3	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	3
	B	2	2	2	2	2	3	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	3
	A	2	2	2	2	2	3	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X74 AND 70299-X74LF	D	1	-	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	B	1	1	-	-	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1	1
	A	1	1	1	1	1	-	1	2	2	2	2	2	1	2	1	1	1	1	-	1	1	1	1	1

[illegible]

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3	projection		title METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT	
CA					0. XX $\pm$ 0.13				
					.XXX $\pm$.051				
				angles	0° $\pm$ 2°				
		dr	T.BRUNGARD	11/19/99		product family		METRAL	code
		engr	M.STRAWSER	11/19/99		size	dwg no	213	
		chr	M.STRAWSER	11/19/99		70299		sheet	
		appd	M.STRAWSER	02/29/00	1:1	A	11		
sheet index	revision sheet								

[illegible][illegible][illegible][illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X80 AND 70299-X80LF	D	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	3	4	3	-	-
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	3	4	3	-	-
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	-	4	-	3	-
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	-	4	-	3	-	-



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X81 AND 70299-X81LF	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	-	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X82 AND 70299-X82LF	D	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	C	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	A	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X83 AND 70299-X83LF	D	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	C	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	A	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X84 AND 70299-X84LF	D	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	3	3	3	3	3	3	3
	C	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	3	4	3	3	3	3	3
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	3	3	3	3	3	3	3	3	3
	A	4	4	4	4	4	4	4	4	4	4	4	4	-	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X85 AND 70299-X85LF	D	3	3	-	3	3	-	3	3	-	3	3	3	-	3	3	-	3	3	3	3	3	3	3	-
	C	3	3	-	3	3	-	3	3	-	3	3	3	-	3	3	-	3	3	3	4	3	3	3	-
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	3	3	3	3	3	3	3	-
	A	3	3	3	3	3	3	3	3	3	3	3	3	-	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X86 AND 70299-X86LF	D	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	3	3	3	3	3	3	3
	C	3	3	-	3	3	-	3	3	-	3	3	3	-	3	3	-	3	3	3	4	3	3	3	3
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3	-	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X87 AND 70299-X87LF	D	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-
	C	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-
	B	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-
	A	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-	3	3	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
70299-X88 AND 70299-X88LF	D	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	6	7	5
	C	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	6	7	5
	B	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	6	7	5
	A	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	6	7	5

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X89 AND 70299-X89LF	D	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
	C	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
	B	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
	A	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X90 AND 70299-X90LF	D	6	6	6	6	6	6	7	6	6	6	6	7	6	6	6	6	6	6	6	6	6	7	7	7
	C	6	6	6	6	6	6	7	6	6	6	6	7	6	6	6	6	6	6	6	6	6	7	7	7
	B	6	6	6	6	6	6	7	6	6	6	6	7	6	6	6	6	6	6	6	6	6	7	7	7
	A	6	6	6	6	6	6	7	6	6	6	6	7	6	6	6	6	6	6	6	6	6	7	7	7

mat'l code				--				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com									
ltr	ecr no.	dr	date	linear	0.X ±0.3			COPY				projection													
CA				linear	0.XX ±0.13			product family				title													
				angles	.XXX ±.051			METRAL				METRAL SIGNAL HEADER													
				dr	0° ±2°			size				4 MOD, 4 ROW PRESS-FIT													
				enrg	T.BRUNGARD 11/19/99			product family				METRAL													
				chr	M.STRAWSE 11/19/99			size				dwg no													
				appd	M.STRAWSE 02/29/00			A				70299													
sheet		revision																							
index		sheet																							



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X91 AND 70299-X91LF	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X92 AND 70299-X92LF	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X93 AND 70299-X93LF	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X94 AND 70299-X94LF	D	3	3	3	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X95 AND 70299-X95LF	D	-	-	-	-	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3
	C	-	-	-	-	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3
	B	-	-	-	-	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3
	A	-	-	-	-	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	4	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X96 AND 70299-X96LF	D	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X97 AND 70299-X97LF	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X98 AND 70299-X98LF	D	45	45	22	45	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22
	C	45	45	45	45	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22
	B	45	45	45	45	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22
	A	45	45	45	45	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X99 AND 70299-X99LF	D	7	7	22	7	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22
	C	7	7	7	7	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22
	B	7	7	7	7	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22
	A	7	7	7	7	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22	22

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X100 AND 70299-X100LF	D	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	19	19	2	3	2	2	2	2	1
	C	2	1	1	2	2	2	2	2	2	2	1	2	2	2	2	2	19	19	2	3	2	2	2	1
	B	2	2	2	2	2	2	2	2	2	19	2	2	2	2	2	2	19	19	2	3	2	2	2	1
	A	1	2	1	1	1	2	2	2	2	1	2	2	2	2	2	2	19	19	2	3	2	2	2	1


mat'l code				--		tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		projection			
CA				linear	0.XX ±0.13					title	
				angles	.XXX ±.051					METRAL SIGNAL HEADER 4 MOD, 4 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99					product family	
				enrg	M.STRAWSE 11/19/99						



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X101 AND 70299-X101LF	D	2	2	2	2	2	2	2	1	2	2	2	1	2	2	2	2	19	19	2	3	2	2	2	19
	C	2	2	2	1	1	2	2	1	2	2	1	2	2	2	2	2	19	19	2	3	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	19	2	2	2	2	2	2	19	19	2	3	2	2	2	19
	A	2	2	1	2	1	2	2	2	2	1	2	2	2	2	2	2	19	19	2	3	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
70299-X102 AND 70299-X102LF	D	1	1	1	1	1	1	1	1	1	3	3	2	2	2	2	2	3	3	2	2	2	2	1
	C	1	1	1	1	1	1	1	1	1	3	3	2	2	2	2	2	3	3	2	2	2	2	1
	B	1	1	1	1	1	1	1	1	1	3	3	2	2	2	2	2	3	3	2	2	2	2	1
	A	1	1	1	1	1	1	1	1	1	3	3	2	2	2	2	2	3	3	2	2	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
70299-X103 AND 70299-X103LF	D	2	2	2	2	2	2	2	2	2	2	3	3	3	2	1	1	2	1	1	2	2	3	3	
	C	2	2	2	2	2	2	2	2	2	2	3	3	3	2	1	1	2	1	1	2	2	3	3	
	B	2	2	2	2	2	2	2	2	2	2	3	3	3	2	1	1	2	1	1	2	2	3	3	
	A	2	2	2	2	2	2	2	2	2	2	3	3	3	2	1	1	2	1	1	2	2	3	3	

mat'l code				--		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com							
lfr	ecn no.	dr	date	linear	0.X ±0.3		COPY				title						
CA					0.XX ±0.13		projection				METRAL SIGNAL HEADER						
					.XXX ±.051						4 MOD, 4 ROW PRESS-FIT						
				angles	0° ±2°						product family		METRAL		code		
				dr	T.BRUNGARD	11/19/99			size		dwg no		213				
				enrg	M.STRAWSER	11/19/99			A		70299		sheet				
				chr	M.STRAWSER	11/19/99			scale								
				appd	M.STRAWSER	02/29/00											
sheet		revision															
index		sheet															

cage code 22526

Pro/E

PDM: Rev:CA

STATUS: Released

Printed: May 16, 2009