

	10	9	8	7	6	5	4	3	2	1																																																																																																												
F	MATERIAL NO. LOOSE PIECE	ENGINEERING P/N LOOSE	MATERIAL NO. TAPE MOUNTED	ENGINEERING P/N TAPED	STUD SIZE	"S" ±.005/0.13	"W" MAX.	"C" MIN.	"L " MAX.	"H" ±.02 /0.5	PARTS ON TAPE	F																																																																																																										
	191930303	G-375-10	-	G-375-10T	10	.198/5.03	.645/16.38	.703/17.86	1.583/40.21	.43/10.9																																																																																																												
	191930305	G-375-14	-	G-375-14T	1/4"	.265/6.73	.645/16.38	.703/17.86	1.583/40.21	.43/10.9																																																																																																												
	191930309	G-375-56	-	G-375-56T	5/16"	.328/8.33	.645/16.38	.703/17.86	1.583/40.21	.43/10.9																																																																																																												
	191930307	G-375-38	-	G-375-38T	3/8"	.390/9.91	.645/16.38	.703/17.86	1.583/40.21	.43/10.9																																																																																																												
	191930297	G-374-14	-	-	1/4"	.265/6.73	.879/22.33	.703/17.86	1.700/43.18	-																																																																																																												
	191930299	G-374-56	-	-	5/16"	.328/8.33	.879/22.33	.703/17.86	1.700/43.18	-																																																																																																												
	191930298	G-374-38	-	-	3/8"	.390/9.91	.879/22.33	.703/17.86	1.700/43.18	-																																																																																																												
E	191930302	G-374-76	-	G-374-76T	7/16"	.453/11.51	.879/22.33	.703/17.86	1.700/43.18	.31/7.9																																																																																																												
	191930296	G-374-12	-	G-374-12T	1/2"	.515/13.08	.879/22.33	.703/17.86	1.700/43.18	.31/7.9																																																																																																												
	191930301	G-374-58	-	G-374-58T	5/8"	.656/16.66	.879/22.33	.703/17.86	1.700/43.18	.31/7.9																																																																																																												
	191930313	G-376-14	-	-	1/4"	.265/6.73	.895/22.73	.990/25.15	1.995/50.67	-																																																																																																												
	191930315	G-376-56	-	-	5/16"	.328/8.33	.895/22.73	.990/25.15	1.995/50.67	-																																																																																																												
	191930314	G-376-38	-	-	3/8"	.390/9.91	.895/22.73	.990/25.15	1.995/50.67	-																																																																																																												
	191930312	G-376-12	-	-	1/2"	.515/13.08	.895/22.73	.990/25.15	1.995/50.67	-																																																																																																												
	191930319	G-377-14	-	-	1/4"	.265/6.73	1.270/32.26	.990/25.15	2.183/55.45	-																																																																																																												
D	191930322	G-377-56	-	-	5/16"	.328/8.33	1.270/32.26	.990/25.15	2.183/55.45	-																																																																																																												
	191930321	G-377-38	-	-	3/8"	.390/9.91	1.270/32.26	.990/25.15	2.183/55.45	-																																																																																																												
	191930324	G-377-76	-	-	7/16"	.453/11.51	1.270/32.26	.990/25.15	2.183/55.45	-																																																																																																												
	191930318	G-377-12	-	-	1/2"	.515/13.08	1.270/32.26	.990/25.15	2.183/55.45	-																																																																																																												
	191930611	G-377-58	-	-	5/8"	.656/16.66	1.270/32.26	.990/25.15	2.183/55.45	-																																																																																																												
	191930320	G-377-34	-	-	3/4"	.781/19.84	1.270/32.26	.990/25.15	2.183/55.45	-																																																																																																												
C											C																																																																																																											
B	NOTES: 1. MATERIAL: MATTE-TIN PLATED COPPER 2. WIRE SIZE: 2 AWG/ 26.6-42.4 mm² 3. PARTS ARE ROHS COMPLIANT. PRE-RELEASE REFERENCE USE ONLY										B																																																																																																											
A	SALES DRAWING REDRAWN FROM SD-19193-007, -028, -029, -030 DRAWN BY DLM 07/2003										A																																																																																																											
	<table><tr><td colspan="4">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td colspan="2">DIMENSION UNITS INCH/MM</td><td colspan="2">SCALE NTS</td><td colspan="2">CURRENT REV DESC: REMOVED OBSOLETE PART NUMBER AS PER PCN#511684.</td><td colspan="4">molex</td></tr><tr><td colspan="4">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2"></td><td colspan="4">RING TONGUE TERMINAL VERSAKRIMP, 2 AWG</td></tr><tr><td colspan="2"></td><td>MM</td><td>INCH</td><td colspan="2"></td><td colspan="4">PRODUCT CUSTOMER DRAWING</td></tr><tr><td>4 PLACES</td><td>±</td><td></td><td>±</td><td colspan="2">EC NO: 748897</td><td colspan="4"></td></tr><tr><td>3 PLACES</td><td>±</td><td></td><td>± 0.005</td><td colspan="2">DRWN: SANTHN 2023/05/09</td><td colspan="4"></td></tr><tr><td>2 PLACES</td><td>±</td><td>0.13</td><td>± 0.01</td><td colspan="2">CHK'D: GGA 2023/05/31</td><td colspan="4"></td></tr><tr><td>1 PLACE</td><td>±</td><td>0.25</td><td>± 0.02</td><td colspan="2">APPR: GGA 2023/05/31</td><td colspan="4"></td></tr><tr><td>0 PLACES</td><td>±</td><td></td><td>±</td><td colspan="2">INITIAL REVISION:</td><td colspan="4">DOCUMENT NUMBER</td></tr><tr><td colspan="4">ANGULAR TOL ± °</td><td colspan="2">THIRD ANGLE PROJECTION</td><td colspan="2">DRAWING</td><td>SERIES</td><td>MATERIAL NUMBER</td><td>CUSTOMER</td><td>SHEET NUMBER</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">B-SIZE</td><td colspan="2">19193</td><td colspan="2">SEE TABLE</td><td colspan="2">GENERAL MARKET 1 OF 1</td></tr></table>										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				DIMENSION UNITS INCH/MM		SCALE NTS		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBER AS PER PCN#511684.		molex				GENERAL TOLERANCES (UNLESS SPECIFIED)						RING TONGUE TERMINAL VERSAKRIMP, 2 AWG						MM	INCH			PRODUCT CUSTOMER DRAWING				4 PLACES	±		±	EC NO: 748897						3 PLACES	±		± 0.005	DRWN: SANTHN 2023/05/09						2 PLACES	±	0.13	± 0.01	CHK'D: GGA 2023/05/31						1 PLACE	±	0.25	± 0.02	APPR: GGA 2023/05/31						0 PLACES	±		±	INITIAL REVISION:		DOCUMENT NUMBER				ANGULAR TOL ± °				THIRD ANGLE PROJECTION		DRAWING		SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				B-SIZE		19193		SEE TABLE		GENERAL MARKET 1 OF 1	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																						
DIMENSION UNITS INCH/MM		SCALE NTS		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBER AS PER PCN#511684.		molex																																																																																																																
GENERAL TOLERANCES (UNLESS SPECIFIED)						RING TONGUE TERMINAL VERSAKRIMP, 2 AWG																																																																																																																
		MM	INCH			PRODUCT CUSTOMER DRAWING																																																																																																																
4 PLACES	±		±	EC NO: 748897																																																																																																																		
3 PLACES	±		± 0.005	DRWN: SANTHN 2023/05/09																																																																																																																		
2 PLACES	±	0.13	± 0.01	CHK'D: GGA 2023/05/31																																																																																																																		
1 PLACE	±	0.25	± 0.02	APPR: GGA 2023/05/31																																																																																																																		
0 PLACES	±		±	INITIAL REVISION:		DOCUMENT NUMBER																																																																																																																
ANGULAR TOL ± °				THIRD ANGLE PROJECTION		DRAWING		SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																																																																																																											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				B-SIZE		19193		SEE TABLE		GENERAL MARKET 1 OF 1																																																																																																												
	DOCUMENT STATUS	P1	RELEASE DATE	2023/05/31 04:48:41																																																																																																																		
	9	8	7	6	5	4	3	2	1																																																																																																													