





REVISION T

NOTES

1. MAX ALLOWABLE BOW: .005 IN/IN [mm/mm] AFTER ASSEMBLY.
2. TERMINAL PUSHOUT FORCE: 2 lbs. MIN.
3. MAX PIN ROTATION IN BODY: 2°.
4. (C) REPRESENTS A CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL USE.
5. CUT FLASH .010 [.25] MAX
6. TUBE POSITIONS 8-50.



DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:
ONE PLACE DECIMALS ± .1 [3]	THREE PLACE DECIMALS ± .005 [.13]	ANGLES	± 2°
TWO PLACE DECIMALS ± .01 [.3]	FOUR PLACE DECIMALS ± .0020 [.051]		

TITLE:

TERMINAL
MICRO STRIP

DWG NO:

MTMS-1XX-XX-XX-X-X-XXX

SHEET 1 OF 1

MTMS-1XX-XX-XX-X-X-XXX

BODY LENGTH SPEC
EXPRESSED IN # POS PER ROWTERMINAL SPEC
SEE TABLE 1

PLATING SPECIFICATION

- G: GOLD, SPECIFY -G IN TERMINAL SUFFIX -XX
- T: TIN, SPECIFY -T IN TERMINAL SUFFIX -XX
- AVAILABLE ON -01, -02, -25, -51, & -52 LEAD STYLES ONLY
- S: SELECTIVE, SPECIFY -S IN TERMINAL SUFFIX -XX
- F: FLASH SELECTIVE GOLD, SPECIFY -F IN TERMINAL SUFFIX -XX
- TM: MATTE TIN, SPECIFY -T IN TERMINAL SUFFIX -XX
- AVAILABLE ON -01, -02, -25, -51, & -52 LEAD STYLES ONLY
- SM: HEAVY GOLD SELECTIVE, SPECIFY -S IN TERMINAL SUFFIX -XX
- FM: FLASH GOLD SELECTIVE, SPECIFY -F IN TERMINAL SUFFIX -XX

POLARIZING OPTION
XXX INDICATES POS. TO BE OMITTED
(SEE FIGURE 1)POST HEIGHT
XXX="A" (SEE TABLE 1)
(SEE 'A' MAX. FOR MAX POST HEIGHT
FOR EACH LEAD STYLE)
(.000 MIN.)ROW OPTION
-S: SINGLE (USE HTMS-50-S)
-D: DOUBLE (USE HTMS-50-D)

TABLE 2

PACKAGING TUBE TABLE (SEE NOTE 6)			
BODY STYLE	LEAD STYLE	TUBE	PLUG
MTMS-DOUBLE STRAIGHT STYLES	-01, -21, -51, -52	PT-1-24-01-22	TP-03
	-02, -25	PT-1-24-05-38	TP-03
	-53	PT-1-24-02-66	TP-03
	-55, -56	PT-1-24-01-29	TP-24
	-54	PT-1-24-02-46	TP-03
	-57	PT-1-24-02-25	TP-03
	-58	PT-1-24-16-29	TP-07
	-59	PT-1-24-16-29	TP-07
	-60	PT-1-24-18-29	TP-07
	-01, -21, -53	PT-1-24-01-24	TP-24
MTMS-SINGLE STRAIGHT STYLES	PT-1-24-10-03	TP-03	
	-58, -59, -60	PT-1-24-01-12	TP-12
	-02, -25	PT-1-24-01-24	TP-24
	-51, -52	PT-1-24-01-24	TP-24
	-54, -55	PT-1-24-02-03	TP-24
	-57	PT-1-24-01-46	TP-24
	PT-1-24-02-03	TP-24	

TABLE 1

LEAD STYLE	TERMINAL SPEC.	'L'	'A' MAX.
-01	T-1M6-18-X-2	.450 [11.43]	.230 [5.84]
-02	T-1M6-17-X-2	.320 [8.13]	.100 [2.54]
-25	T-1M6-25-X-2	.330 [8.38]	.125 [3.18]
-51	T-1M6-02-X-2	.410 [10.41]	.190 [4.83]
-52	T-1M6-12-X-2	.425 [10.80]	.205 [5.21]
-53	T-1M6-04-X-2	.505 [12.83]	.285 [7.24]
-54	T-1M6-14-X-2	.555 [14.10]	.335 [8.51]
-55	T-1M6-03-X-2	.610 [15.49]	.390 [9.91]
-56	T-1M6-13-X-2	.625 [15.88]	.405 [10.29]
-57	T-1M6-19-X-2	.650 [16.51]	.430 [10.92]
-58	T-1M6-05-X-2	.705 [17.91]	.485 [12.32]
-59	T-1M6-15-X-2	.755 [19.18]	.535 [13.59]
-60	T-1M6-16-X-2	.825 [20.96]	.605 [15.37]

samtecEXISPROD/ASSEMBLY/050
MTMS-ASM520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322MADE BY: GREG REIDINGER 5-8-91
CHECKED BY: McCARTINENG. APPROVAL
DEMMTMS-1XX-XX-XX-X-X-XXX
SHEET 1 OF 1

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

Do not scale
from this print