



Switches > Tactile Switches



Actuator Style: **Rectangular**

Operating Function: **Off (On)**

Contact Base Material: **Brass**

Switch Contact Plating Material: **Silver**

Contact Current Rating: **50 mA**

Features

Product Type Features

Illuminated	With
Actuator Style	Rectangular

Configuration Features

Operating Function	Off (On)
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Body Features

Actuator Force	160 g[5.64 oz]
Product Orientation	Vertical
Actuator Color	Brown

Contact Features

Contact Base Material	Brass
Switch Contact Plating Material	Silver
Contact Current Rating	50 mA

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Housing Features

--	--



Process Sealed	No
----------------	----

Usage Conditions

Operating Temperature Range	-25 – 70 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 5-2213819-3
6X6 ILL TACT SMT 520GF LI SOFT
ORANGE



TE Part # 2-2213819-9
6X6 ILL TACT SMT 160GF HI SOFT
ORANGE



TE Part # 4-2213819-5
6X6 ILL TACT SMT 260GF HI SOFT
ORANGE



TE Part # 4-2213819-8
6X6 ILL TACT SMT 260GF HI COLD
WHITE





TE Part # 2-2213819-3
6X6 ILL TACT SMT 160GF LI RED


Also in the Series

Alcoswitch FSMIJ



Tactile Switches(128)

Customers Also Bought

 TE Part #1658622-9 40 NOVO MIL/CTR 30DP,LEAD FREE	 TE Part #746611-8 14 DIP PLUG CONN-W/COVER	TE Part #1SNA164922R1000 BRE-T-1.5	TE Part #1SNA166516R1300 FIM10-1
TE Part #1SNA166525R1400 FIC-2/4-1	TE Part #1SNA166546R2100 FIT-1/4-D	TE Part #1SNA166737R2000 CC-E-VA	TE Part #1SNA167260R1700 BRE-C-2.5
TE Part #1SNA168010R0100 PROTECTEUR M20	TE Part #1SNS440000Z0028 CAPOTS 17938707+ DOIGTS 16498417		



Documents

Product Drawings

6X6 ILL TACT THT 160GF HI COLD WHITE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2213818-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2213818-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2213818-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English