



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Wire-to-Wire**

Lead Wire Size: **.5 – 1.3 mm²**

Magnet Wire Size: **.56 – 1.83 mm**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Wire-to-Wire
Terminal Plating Material	Unplated
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Dimensions

Terminal Height	6.1 mm[.24 in]
Lead Wire Size	.5 – 1.3 mm²
Magnet Wire Size	.56 – 1.83 mm
Stock Thickness (Magnet Wire Side)	.81 mm[.032 in]
Product Length	13.97 mm[.55 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------



Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1601137-2
151-003-014=WIRE2BLADE,MED,SMZ

TE Part # 1601436
551-001-000=POCKET DETAIL



Also in the Series | [SIAMEZE](#)



[Insertion & Extraction Tools\(1\)](#)



[Magnet Wire Terminals\(192\)](#)


Customers Also Bought



[TE Part #2-1393243-4](#)
[RTE25524](#)



[TE Part #964339-1](#)
[MAG MATE KONT. MKII](#)



[TE Part #1-1546111-0](#)
[EUROSTYLE TB,HEADER,GREY,10POS](#)



[TE Part #5822138-4](#)
[80 ME .050 L/P AU M/L PB-FREE](#)



[TE Part #9-2176374-8](#)
[RQ 0805 1K1 0.1% 10PPM 1K RL](#)

Documents

Product Drawings

[WIRE2WIRE,MEDIUM,SMZ](#)

English

[WIRE2WIRE,MEDIUM,SMZ](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1601136-1_D_c-1601136-1-d.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1601136-1_D_c-1601136-1-d.3d_igs.zip](#)

English



Customer View Model

[ENG_CVM_CVM_1601136-1_D_c-1601136-1-d.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Magnet Wire Terminals & Splices

English

[1-1773702-7 _IDC_Magnet_Wire](#)

English

Product Specifications

[Application Specification](#)

English