






NOTES

1. RE DETAILED DIMENSION, SEE PRODUCT DRAWING.
2. NUMBER OF CONNECTORS : 8000 PCS/REEL.
3. LEAD TAPE LENGTH.




4. TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3
5. MATERIAL
CARRER TAPE :POLYSTYRENE
TOP TAPE :PET , OTHER
REEL :POLYSTYRENE(PS)(RECYCLE MATERIAL CONTAINED)

MODEL NO. 505066-**22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
CURRENT REV DESC:		molex							
0.35 BB CONN. H=0.6 SSB6 RP REC ASSY									
PRODUCT CUSTOMER DRAWING									
DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION			
5050660000		PSD		008		E			
MATERIAL NUMBER		CUSTOMER				SHEET NUMBER			
SEE TABLE		GENERAL				1 OF 3			

DIMENSION UNITS		SCALE	
mm		1:5	
GENERAL TOLERANCES (UNLESS SPECIFIED)			
ANGULAR TOL		±	1.0 °
4 PLACES		±	0.01
3 PLACES		±	0.03
2 PLACES		±	0.05
1 PLACE		±	0.1
0 PLACES		±	0.2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			

EC NO: 730166			
DRWN: RAJAGN		2022/11/28	
CHK'D: YNUKANOBU		2022/11/30	
APPR: YNAITO		2022/11/30	
INITIAL REVISION:			
DRWN: TNISHIDA02		2017/03/28	
APPR: TKUSUHARA01		2017/04/03	
THIRD ANGLE PROJECTION		DRAWING	
		SERIES	
A3-SIZE		505066	



24	29.4	25.4	13.77	505066-6422	---	---	64
			13.07	505066-6022	---	---	60
			12.02	505066-5422	○	---	54
			11.32	505066-5022	○	---	50
			10.99	505066-4822	○	---	48
			10.62	505066-4622	---	---	46
			9.92	505066-4222	○	---	42
			9.57	505066-4022	○	---	40
			8.52	505066-3422	○	---	34
			8.17	505066-3222	---	---	32
キャリアテープ幅 CARRIER TAPE WIDTH	C	B	(A)	MATERIAL No.	HIGH VOL TOOL	LOW VOL TOOL	CIRCUIT
				SAMPLE PREPARATION			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	2:1
GENERAL TOLERANCES (UNLESS SPECIFIED)	
ANGULAR TOL	± 1.0 °
4 PLACES	± 0.01
3 PLACES	± 0.03
2 PLACES	± 0.05
1 PLACE	± 0.1
0 PLACES	± 0.2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

CURRENT REV DESC:

EC NO: 730166
DRWN: RAJAGN
CHK'D: YNUKANOBU
APPR: YNAITO

INITIAL REVISION:
DRWN: TNISHIDA02
APPR: TKUSUHARA01

THIRD ANGLE PROJECTION

DRAWING
A3-SIZE

SERIES
505066

MATERIAL NUMBER
SEE TABLE

CUSTOMER
GENERAL

SHEET NUMBER
3 OF 3

molex

0.35 BB CONN. H=0.6 SSB6 RP REC ASSY


PRODUCT CUSTOMER DRAWING


DOCUMENT NUMBER
5050660000

DOC TYPE
PSD

DOC PART
008


REVISION
E






RECOMMENDED P.W.BOARD PATTERN LAYOUT (REFERENCE)

 PROHIBITED AREA OF PATTERN WIRING AND SOLDER
(FOR EACH AREA, THE WIRING THAT TOUCHES ON THE SOLDER
CAN BE ATTACHED, THEN COVERED WITH A FILM TO KEEP SOLDER OUT)



MATED CONDITION



RECOMMENDED METAL MASK LAYOUT (REFERENCE)

RECOMMENDED THICKNESS OF METAL MASK : $t=0.08\text{mm}$

RECEMMENDED OPEN APERTURE RATIO OF METAL MASK : 80%

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED				molex			
mm		20:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)				0.35 BB CONN. H=0.6 SSB6 RP							
ANGULAR TOL ± 1.0°											
4 PLACES ± 0.001											
3 PLACES ± 0.003				PRODUCT CUSTOMER DRAWING							
2 PLACES ± 0.03											
1 PLACE ± 0.1				DOCUMENT NUMBER 5050661000							
0 PLACES ± 0.2											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER	
								A3-SIZE		CUSTOMER	
						505066		GENERAL		SHEET NUMBER	
								2 OF 2			