

2-323912-1

✓ ACTIVE


PIDG

TE Internal #: 2-323912-1

Closed Ring Tongue Terminal, 26 – 22 AWG, #2 / M2 Stud Size, 2.36 mm [.093 in] Stud Diameter, Closed Barrel, Straight, Tin, Partially Insulated

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals

Ring Terminal Product Type: **Closed Ring Tongue Terminal**Wire Size: **202 – 810 CMA**Stud Size: **#2, M2**[All PIDG Ring Tongue Terminals \(411\)](#)**Features****Product Type Features**

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#2, M2
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Product Weight	.222 g
----------------	--------

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight

Terminal Plating Material

Tin

Mechanical Attachment

Wire Insulation Support

With

Dimensions

Wire Size

202 – 810 CMA

Stud Diameter

2.36 mm [.093 in]

Tongue Thickness

.79 mm [.031 in]

Product Length

13.33 mm [.525 in]

Compatible Insulation Diameter (Max)

2.08 mm [.082 in]

Compatible Insulation Diameter Range

1.27 – 2.08 mm [.05 – .082 in]

Usage Conditions

Insulation Option

Partially Insulated

Operating Temperature Range

105 °C [221 °F]

Operation/Application

Compatible With Wire Base Material

Copper

Compatible With Wire Plating Material

Tin

Industry Standards

Government Qualified Terminal

No

Packaging Features

Packaging Quantity

4000

Packaging Method

Tape Mounted

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46121
DAHT PG PIDG 26-22 ASSY


Also in the Series | PIDG




Compression Connectors(17)




Crimp Wire Pins, Tabs & Ferrules(41)




Hand Crimping Tools(2)




Knife Disconnects(11)




Quick Disconnects(32)



Ring Terminals(589)



Spade Terminals(228)



Special Purpose Terminals(1)



Splices(40)

Customers Also Bought



TE Part #206486-2
 CPC RECPT ASSEMBLY SIZE 11-9



TE Part #323912
 TERMINAL,PIDG R 26-22 2



TE Part #322777
 PIDG SPDFLG 22-16COMM22-18MIL6



TE Part #9-1437622-6
 KPN700B1/4-KNOB BLK W/POINTER



TE Part #1-1589061-3
 QCM019SC2DMC30P = CIRCULAR



TE Part #YDTS26F09-35SNV001
 PLUG ASSY



TE Part #2-1393030-2
 SSRT-240D25 = PANEL MOUNT,25A,
 240VAC



TE Part #625159-000
 D-110-35



TE Part #ABC03G-20P-4048
 IN-LINE RECIP



TE Part #2-2106124-3
 CONTACT, SEALED LIGHTING
 CONN, 22-24 AWG

Documents

Product Drawings

[TERMINAL,PIDG R 26-22 2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-323912-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-323912-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-323912-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English