
HVU350

Variable Capacitance Diode for VCO

HITACHI

ADE-208-036D (Z)
Rev. 4


Features

- Low series resistance. ($r_s = 0.50\Omega_{\text{max}}$)
- Ultra small Resin Package (URP) is suitable for surface mount design.

Ordering Information

Type No.	Laser Mark	Package Code
HVU350	4	URP

Outline



HVU350

Absolute Maximum Ratings (Ta = 25°C)

Item	Symbol	Value	Unit
Reverse voltage	V_R	15	V
Junction temperature	T_j	125	°C
Storage temperature	T_{stg}	–55 to +125	°C

Electrical Characteristics (Ta = 25°C)

Item	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse current	I_{R1}	—	—	10	nA	$V_R = 15V$
	I_{R2}	—	—	100		$V_R = 15V, T_a = 60°C$
Capacitance	C_1	15.0	—	17.5	pF	$V_R = 1V, f = 1MHz$
	C_4	5.3	—	6.3		$V_R = 4V, f = 1MHz$
Capacitance ratio	n	2.80	—	—	—	C_1/C_4
Series resistance	r_s	—	—	0.50	Ω	$V_R = 1V, f = 470MHz$




Fig.1 Reverse current Vs. Reverse voltage




Fig.2 Capacitance Vs. Reverse voltage




Fig.3 Series resistance Vs. Reverse voltage





Fig.4 Linearity factor Vs. Reverse voltage

Package Dimensions

Unit: mm



- 1 Cathode
- 2 Anode

HITACHI Code	URP
JEDEC Code	—
EIAJ Code	—
Weight (g)	0.004