

PESD12VSA-L

Very low capacitance bidirectional ESD protection diode

24 April 2018

Product data sheet

1. General description

Very low capacitance bidirectional ElectroStatic Discharge (ESD) protection diode designed to protect one signal line from the damage caused by ESD and other transients. The device is housed in a leadless ultra small DFN1006-2 (SOD882) Surface-Mounted Device (SMD) plastic package.

2. Features and benefits

- · Bidirectional ESD protection of one line
- Low diode capacitance C_d = 17 pF
- Rated peak pulse power: P_{PPM} = 290 W
- Ultra low leakage current I_{RM} < 1 nA
- ESD protection up to 25 kV
- IEC 61000-4-2; level 4 (ESD)
- IEC 61000-4-5 (surge); I_{PPM} = 7.5 A
- AEC-Q101 qualified

3. Applications

- · Computers and peripherals
- · Audio and video equipment
- · Cellular handsets and accessories
- · Portable electronics
- Communication systems

4. Quick reference data

Table 1. Quick reference data

| able 1: Quion reference data | | | | | | | |
|------------------------------|--------------------------|---|--|-----|-----|-----|------|
| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
| V_{RWM} | reverse standoff voltage | T _{amb} = 25 °C | | - | - | 12 | V |
| C _d | diode capacitance | f = 1 MHz; V _R = 0 V; T _{amb} = 25 °C | | - | 17 | 25 | pF |



Very low capacitance bidirectional ESD protection diode

5. Pinning information

Table 2. Pinning information

| Pin | Symbol | Description | Simplified outline | Graphic symbol |
|-----|--------|-------------|-------------------------|----------------|
| 1 | K | cathode | | 1 2 2 |
| 2 | K | cathode | | sym045 |
| | | | Transparent top view | |
| | | | DFN1006-2 (SOD882) | |

6. Ordering information

Table 3. Ordering information

| Type number | Package | | | | | | |
|-------------|-----------|--|---------|--|--|--|--|
| | Name | Description | Version | | | | |
| PESD12VSA-L | DFN1006-2 | DFN1006-2: leadless ultra small plastic package; 2 terminals | SOD882 | | | | |

7. Marking

Table 4. Marking codes

| able it marking seaso | | | | |
|-----------------------|--------------|--|--|--|
| Type number | Marking code | | | |
| PESD12VSA-L | MW | | | |

8. Limiting values

Table 5. Limiting values


In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol | Parameter | Conditions | | Min | Max | Unit |
|------------------|--------------------------|----------------------------------|-----|-----|-----|------|
| P _{PPM} | rated peak pulse power | | [1] | - | 290 | W |
| I _{PPM} | rated peak pulse current | t _p = 8/20 μs | [1] | - | 7.5 | Α |
| Tj | junction temperature | | | - | 150 | °C |
| T _{amb} | ambient temperature | | | -55 | 150 | °C |
| T _{stg} | storage temperature | | | -65 | 150 | °C |
| ESD maximu | um ratings | | | , | , | |
| V _{ESD} | electrostatic discharge | IEC 61000-4-2; contact discharge | [2] | - | 25 | kV |
| | voltage | machine model | | - | 400 | V |
| | | human body model (MIL-STD-883) | | - | 10 | kV |

^[1] Device stressed with non-repetitive current pulses (8/20 μs exponential decay waveform according to IEC 61000-4-5 and IEC 61643-321).

^[2] Device stressed with ten non-repetitive ESD pulses.

Very low capacitance bidirectional ESD protection diode



8/20 µs pulse waveform according to IEC 61000-4-5 and IEC 61643-321




Fig. 2. ESD pulse waveform according to IEC 61000-4-2

9. Characteristics

Table 6. Characteristics

| | Taoteriotics | | | _ | _ | _ | |
|------------------|--------------------------|---|-----|------|-----|-----|------|
| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
| V_{RWM} | reverse standoff voltage | T _{amb} = 25 °C | | - | - | 12 | V |
| V_{BR} | breakdown voltage | I _R = 5 mA; T _{amb} = 25 °C | | 14.5 | - | - | V |
| I _{RM} | reverse leakage current | V _{RWM} = 12 V; T _{amb} = 25 °C | | - | 1 | 100 | nA |
| C _d | diode capacitance | f = 1 MHz; V _R = 0 V; T _{amb} = 25 °C | | - | 17 | 25 | pF |
| V _{CL} | clamping voltage | I _{PP} = 1 A; T _{amb} = 25 °C | [1] | - | - | 22 | V |
| | | I _{PPM} = 7.5 A; T _{amb} = 25 °C | [1] | - | - | 38 | V |
| R _{dyn} | dynamic resistance | I _R = 10 A; T _{amb} = 25 °C | [2] | - | 0.7 | - | Ω |

Device stressed with 8/20 μ s exponential decay waveform according to IEC 61000-4-5 and IEC 61643-321. Non-repetitive current pulse, Transmission Line Pulse (TLP) t_p = 100 ns; square pulse; ANSI / ESD STM5.5.1-2008.

Very low capacitance bidirectional ESD protection diode







Fig. 3. Rated peak pulse power as a function of square pulse duration; maximum values



J. 4. Diode capacitance as a function of reverse voltage; typical values




Very low capacitance bidirectional ESD protection diode



Very low capacitance bidirectional ESD protection diode

10. Application information

The device is designed for the protection of one bidirectional data line from surge pulses and ESD damage. The device is suitable on lines where the signal polarities are both positive and negative with respect to ground.



Circuit board layout and protection device placement

Circuit board layout is critical for the suppression of ESD, Electrical Fast Transient (EFT) and surge transients. The following guidelines are recommended:

- 1. Place the device as close to the input terminal or connector as possible.
- 2. Minimize the path length between the device and the protected line.
- 3. Keep parallel signal paths to a minimum.
- 4. Avoid running protected conductors in parallel with unprotected conductors.
- 5. Minimize all Printed-Circuit Board (PCB) conductive loops including power and ground loops.
- 6. Minimize the length of the transient return path to ground.
- 7. Avoid using shared transient return paths to a common ground point.
- 8. Use ground planes whenever possible. For multilayer PCBs, use ground vias.


11. Test information

Quality information


This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - Stress test qualification for discrete semiconductors, and is suitable for use in automotive applications.

Very low capacitance bidirectional ESD protection diode

12. Package outline



13. Soldering



Very low capacitance bidirectional ESD protection diode

14. Revision history

Table 7. Revision history

| Data sheet ID | Release date | Data sheet status | Change notice | Supersedes |
|-----------------|--------------|--------------------|---------------|------------|
| PESD12VSA-L v.1 | 20180424 | Product data sheet | - | - |

Very low capacitance bidirectional ESD protection diode

15. Legal information

Data sheet status

| Document status [1][2] | Product status [3] | Definition |
|--------------------------------------|--------------------|---|
| Objective [short] data sheet | Development | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification | This document contains data from the preliminary specification. |
| Product [short] data sheet | Production | This document contains the product specification. |

- Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

Definitions

Preview — The document is a preview version only. The document is still subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This Nexperia product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

PESD12VSA-L

All information provided in this document is subject to legal disclaimers.

© Nexperia B.V. 2018. All rights reserved

Very low capacitance bidirectional ESD protection diode

Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Very low capacitance bidirectional ESD protection diode

16. Contents

| 1. | General description | 1 |
|-----|-------------------------|---|
| 2. | Features and benefits | 1 |
| 3. | Applications | 1 |
| 4. | Quick reference data | 1 |
| 5. | Pinning information | 2 |
| 6. | Ordering information | 2 |
| 7. | Marking | 2 |
| 8. | Limiting values | 2 |
| 9. | Characteristics | 3 |
| 10. | Application information | 6 |
| 11. | . Test information | 6 |
| 12. | Package outline | 7 |
| 13. | . Soldering | 7 |
| 14. | Revision history | 8 |
| 15. | Legal information | 9 |
| | | |

[©] Nexperia B.V. 2018. All rights reserved