



STARTER,FVNR,S0,3PH,THOLR,24VAC,N3R/4/12

product brand name	Siemens
product designation	Non-reversing motor starter
special product feature	No factory installed accessories
General technical data	
weight [lb]	15 lb
Height x Width x Depth [in]	12 × 10 × 6 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6 560 ft
country of origin	Germany
Power and control electronics	
number of poles for main current circuit	3
type of voltage of the control supply voltage	AC
control supply voltage	
• at AC at 50 Hz rated value	24 V
• at AC at 60 Hz rated value	24 V
disconnecter functionality	No
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	7.5 hp
• at 220/230 V rated value	7.5 hp
• at 460/480 V rated value	15 hp
• at 575/600 V rated value	20 hp
Contactors	
number of NO contacts for main contacts	3
operating voltage for main current circuit at AC at 60 Hz maximum	600 V
operating voltage at AC-3 rated value maximum	600 V
mechanical service life (operating cycles) of the main contacts typical	10 000 000
Auxiliary contact	
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
number of total auxiliary contacts maximum	8
contact rating of auxiliary contacts of contactor according to UL	10A@600V(A600), 2.5A@600V(Q600)
Coil	
apparent pick-up power of magnet coil at AC	79 VA
apparent holding power of magnet coil at AC	8.5 VA
operating range factor control supply voltage rated value of magnet coil	0.8 ... 1.1
ON-delay time	8 ... 40 ms
OFF-delay time	4 ... 16 ms
Overload relay	

product function			
• overload protection	Yes		
• test function	Yes		
• external reset	Yes		
reset function	Manual, automatic and remote (with optional accessory)		
adjustment range of thermal overload trip unit	20 ... 25		
number of NC contacts of auxiliary contacts of overload relay	1		
number of NO contacts of auxiliary contacts of overload relay	1		
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)		
Enclosure			
degree of protection NEMA rating of the enclosure	NEMA 3/3R/4/12 enclosure		
design of the housing	Dust- & watertight for outdoor use		
Mounting/wiring			
mounting position	vertical		
fastening method	Surface mounting and installation		
type of electrical connection for supply voltage line-side	Screw-type terminals		
tightening torque [lbf-in] for supply	18 ... 21 lbf-in		
type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded	2x (16 ... 12), 2x (14 ... 8)		
temperature of the conductor for supply maximum permissible	60 °C		
material of the conductor for supply	CU		
type of electrical connection for load-side outgoing feeder	Screw-type terminals		
tightening torque [lbf-in] for load-side outgoing feeder	18 ... 21 lbf-in		
type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded	2x (16 ... 12), 2x (14 ... 8)		
temperature of the conductor for load-side outgoing feeder maximum permissible	60 °C		
material of the conductor for load-side outgoing feeder	CU		
type of electrical connection of magnet coil	Screw-type terminals		
tightening torque [lbf-in] at magnet coil	7 ... 10 lbf-in		
type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded	2x (16 ... 12), 2x (14 ... 8)		
temperature of the conductor at magnet coil maximum permissible	75 °C		
material of the conductor at magnet coil	CU		
type of electrical connection for auxiliary contacts	Screw-type terminals		
tightening torque [lbf-in] at contactor for auxiliary contacts	7 ... 10 lbf-in		
type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded	2x (20 ... 16), 2x (18 ... 14)		
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C		
material of the conductor at contactor for auxiliary contacts	CU		
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals		
tightening torque [lbf-in] at overload relay for auxiliary contacts	7 ... 10 lbf-in		
type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded	2x (20 ... 16), 2x (18 ... 14)		
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	70 °C		
material of the conductor at overload relay for auxiliary contacts	CU		
Short-circuit current rating			
design of the fuse link for short-circuit protection of the main circuit required	Class J		
design of the short-circuit trip	Thermal magnetic circuit breaker		
maximum short-circuit current breaking capacity (Icu)			
• at 240 V	5 kA		
• at 480 V	5 kA		
• at 600 V	5 kA		
certificate of suitability	UL 60947-4-1		
Approvals Certificates			
General Product Approval	Test Certificates	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=3RE4122-6CA11-4DY0>

Search Datasheet in Service&Support (Manuals)

<https://support.industry.siemens.com/cs/US/en/ps/3RE4122-6CA11-4DY0/man>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RE4122-6CA11-4DY0&lang=en

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/3RE4122-6CA11-4DY0/certificate>



