

1420824  
<https://www.phoenixcontact.com/us/products/1420824>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, M12, Front mounting, THR- und Wellenlötkontakte, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239324

Your advantages

- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Efficient PCB assembly: two-piece connectors for THR soldering

Commercial data

Item number	1420824
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB23
Product key	ABQACE
GTIN	4055626280516
Weight per piece (including packing)	7.87 g
Weight per piece (excluding packing)	7.79 g
Customs tariff number	85366990
Country of origin	DE

# SACC-FP-M-M12/M14 THR PW - Housing screw connection



1420824

<https://www.phoenixcontact.com/us/products/1420824>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Panel mounting base
Thread type	M12

### Data management status

Article revision	00
------------------	----

### Connection data

Connection method	THR- und Wellenlötkontakte
Tightening torque	1.5 ... 2 Nm

### Material specifications

Material	Brass, nickel-plated
Flammability rating according to UL 94	V0
Seal material	FKM

### Connector

#### Connection 1

Head design	Pin
Head thread type	M12

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked) IP67, when in locked state
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation)

### Mounting

Mounting type	Front mounting
---------------	----------------

# SACC-FP-M-M12/M14 THR PW - Housing screw connection



1420824  
<https://www.phoenixcontact.com/us/products/1420824>

Thread type	()
-------------	----

# SACC-FP-M-M12/M14 THR PW - Housing screw connection



1420824  
<https://www.phoenixcontact.com/us/products/1420824>

## Classifications

### ECLASS

ECLASS-11.0	27440224
ECLASS-12.0	27440224
ECLASS-13.0	27440224

### ETIM

ETIM 9.0	EC003556
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-FP-M-M12/M14 THR PW - Housing screw connection



1420824

<https://www.phoenixcontact.com/us/products/1420824>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	59eedfbc-f4f1-48e8-95d8-86040d7bf30a

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)