



Connectors > Terminal Blocks & Strips > Modular Terminal Blocks



Block Function: **Feed-Through & Pluggable**
Modular Terminal Block Product Type: **Screw Clamp Terminal Block**
Primary Product Color: **Gray**
Product Spacing: **5.2 mm [.205 in]**
Number of Positions: **4**

Features

Product Type Features

Modular Terminal Block Product Type	Screw Clamp Terminal Block
-------------------------------------	----------------------------

Configuration Features

Gauge Type	A3-B3
Number of Levels	1
Number of Circuits	1
Block Function	Feed-Through & Pluggable
Number of Positions	4

Electrical Characteristics

Impulse Withstanding Voltage Rating (IEC)	8000 V
Current Rating (CSA)	28 A
Power Loss	1 W
Short-Time Withstanding Current Rating @ 1s	480 A
Voltage Rating (IEC)	800 V
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	300 V



Voltage Rating (CSA)	300 V
Dielectric Withstanding Voltage (Max)	2200 V
Current Rating (UL)	28 A
Current Rating (IEC)	29 A

Body Features

Product Weight	10.75 g[.429 oz]
Primary Product Color	Gray

Mechanical Attachment

DIN Rail Mounting Type	TH35-15, TH35-7.5
Connector Mounting Type	DIN Rail

Housing Features

Housing Material	Polyamide
------------------	-----------

Dimensions

Main Circuit Capacity - Twin Ferrule per Screw Clamp	24 – 16 AWG
Main Circuit Capacity - 1 Flexible Conductor per Screw Clamp	.22 – 4 mm ²
Main Circuit Capacity - 1 Non-Insulated Ferrule per Screw Clamp	.22 – 4 mm ²
Main Circuit Capacity - 1 Insulated Ferrule per Screw Clamp	24 – 12 AWG
Main Circuit Capacity - 1 Rigid Stranded Conductor per Screw Clamp	24 – 10 AWG
Wire Stripping Length	10.5 mm[.413 in]
Main Circuit Capacity - 2 Rigid Stranded Conductors per Screw Clamp	.2 – 1.5 mm ²
Main Circuit Capacity - 2 Flexible Conductors per Screw Clamp	.22 – 1.5 mm ²
Tool Size	3.5 mm[.138 in]
Product Depth	47.4 mm
Product Length	80.3 mm
Product Height	80.3 mm
Product Spacing	5.2 mm[.205 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Industry Standards

IP Rating	IP20
-----------	------



UL Flammability Rating

UL 94V-0

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1SNK140000R0000 MC512	 TE Part # 1SNK140004R0000 MC512-YL	 TE Part # 1SNK805714R0000 CDS4	 TE Part # 1SNK805715R0000 CDS4-E
--	---	---	---









 TE Part # 1SNK805911R0000 EDS4-22	 TE Part # 1SNK900001R0000 BAM4	 TE Part # 1SNK900002R0000 BAZ1	 TE Part # 1SNK900102R0000 BAZH1
 TE Part # 1SNK900107R0000 CS-R3	 TE Part # 1SNK900200R0000 TC5	 TE Part # 1SNK900203R0000 TP2	 TE Part # 1SNK900205R0000 TP4
 TE Part # 1SNK900606R0000 LH-J	 TE Part # 1SNK900636R0000 COP-ZD	 TE Part # 1SNK900637R0000 VR-ZD	 TE Part # 1SNK905302R0000 JB5-2
 TE Part # 1SNK905303R0000 JB5-3	 TE Part # 1SNK905305R0000 JB5-5	 TE Part # 1SNA164800R0300 PR3.G2	 TE Part # 1SNA168500R1200 PR4

Also in the Series | ENTRELEC SNK

 Modular Terminal Blocks(320)	 Terminal Block & Strip Conducting Accessories(67)	 Terminal Block & Strip Insulating Accessories(31)
---	--	--

Customers Also Bought



 TE Part #1SNK506010R0000 ZS6	 TE Part #1SNK516010R0000 ZS35	 TE Part #1SNA115116R0700 M4/6	 TE Part #1SNA173220R0500 PR30
 TE Part #1SNA233000R0100 RC610	 TE Part #1SNA116656R2500 FEM8D1	 TE Part #1SNA166778R1100 COR-C-R2-6.6	 TE Part #1-2186559-1 1966-RIBBON-NAR
 TE Part #1SNA193629R2000 FEMT2-BE	 TE Part #1SNA195639R2400 M6/8.ST1.V0.IP20		

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK805013R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK805013R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK805013R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English



[ZDS4-22](#)

English

[SNK SERIES TERMINAL BLOCKS](#)

English

[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)

[Essential Entrelec Terminal Blocks](#)

French

[Essential Entrelec Terminal Blocks](#)

English

[Essential Entrelec Terminal Blocks](#)

Japanese

[Agency Approvals](#)

[UL](#)

English