

**Part Number :** 1601126040

**Product Description :** MX150 Hybrid Mat-Sealed Male Connector Assembly, Dual Row, 12 Circuits, UL 94V-0, Keying Option A, Positions 1, 3, 4, 5, 6, and 7 Blocked, Black

**Series Number :** 160112

**Status :** Active

**Product Category :** Connector Housings

**Engineering Number :** CVP-1601126040



## Documents & Resources

### Drawings

[1601126040\\_sd.pdf](#)

[1601129900-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Housings
Series	160112
Description	MX150 Hybrid Mat-Sealed Male Connector Assembly, Dual Row, 12 Circuits, UL 94V-0, Keying Option A, Positions 1, 3, 4, 5, 6, and 7 Blocked, Black
Application	Power, Wire-to-Wire, Automotive
Product Name	MX150
UPC	191130340521

#### Physical

Circuits (maximum)	12
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	22.660/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MX150 Hybrid Mat-Sealed, Dual Row, Female Connector Assemblies	<u>160111</u>

### Use with Part(s)

Description	Part Number
MX150 Male Terminals	<u>33000</u>
MX150 Male Terminals	<u>33011</u>
Use With	Industry Standard Terminal 2.80mm

---

---

This document was generated on Oct 14, 2024