



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: Cable Clamp

Primary Product Material: Stainless Steel

Number of Positions: 75

Thread Size: 8-32

Packaging Method: Bag

Features

Product Type Features

|                              |             |
|------------------------------|-------------|
| Strain Relief Accessory Type | Cable Clamp |
|------------------------------|-------------|

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 75 |
|---------------------|----|

Body Features

|                          |                 |
|--------------------------|-----------------|
| Cable Exit Angle         | 180°, 90°       |
| Primary Product Material | Stainless Steel |

Mechanical Attachment

|             |      |
|-------------|------|
| Thread Size | 8-32 |
|-------------|------|

Dimensions

|                |          |
|----------------|----------|
| Product Length | 95.44 mm |
| Product Height | 65.86 mm |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 150 °C[-67 – 302 °F] |
|-----------------------------|----------------------------|

Packaging Features

|  |  |
|--|--|
|  |  |
|--|--|



|                    |     |
|--------------------|-----|
| Packaging Method   | Bag |
| Packaging Quantity | 1   |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                            |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP M Series



|                                    |                                  |                        |                             |
|------------------------------------|----------------------------------|------------------------|-----------------------------|
|                                    |                                  |                        |                             |
| Board-to-Board Jumpers & Shunts(7) | Connector Caps & Covers(12)      | Connector Hardware(18) | Connector Strain Relief(11) |
|                                    |                                  |                        |                             |
| Rack & Panel Connectors(1)         | Rectangular Power Connectors(65) |                        |                             |

Customers Also Bought

|                                                      |                                                                  |                                                     |                                                      |
|------------------------------------------------------|------------------------------------------------------------------|-----------------------------------------------------|------------------------------------------------------|
|                                                      |                                                                  |                                                     |                                                      |
| TE Part #66361-3<br>III+ PIN,18-14,15AU/FL,LP        | TE Part #1490414-3<br>HYP10 SOLIS HD 1/0AWG INDENTER             | TE Part #58545-1<br>SOLISTRAND 10-22 DIE ASSY       | TE Part #201089-4<br>SERIES" M" JACKSCREW SOCKET ASS |
|                                                      |                                                                  |                                                     |                                                      |
| TE Part #1-201046-2<br>SERIES "M" MIN RECT GUIDE PIN | TE Part #3-1393104-4<br>KRPA-11AN-240=KRPA                       | TE Part #201047-2<br>SERIES "M" ST. STL. GUIDE SOC. | TE Part #31812<br>TERMINAL,SOLIS R 4 3/8             |
|                                                      |                                                                  |                                                     |                                                      |
| TE Part #201501-1<br>SPIROL PIN                      | TE Part #114022-E<br>ERMB 125 FS 1 EED9 * 3,70 A-E V-V *<br>* 24 |                                                     |                                                      |

Documents



Product Drawings

STRAIN RELIEF CLAMP UNASSEM.

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_201848-5\_L.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_201848-5\_L.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_201848-5\_L.3d\_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

STRAIN RELIEF CLAMP CATALOG NO. 201848-[] FOR AMP SERIES "M" CONN

English