

2325106-1

✓ ACTIVE


enetSEAL+ | enetSEAL+

TE Internal #: 2325106-1

Housing for Male Terminals, Wire-to-Wire, 2 Position, 2.54 mm [.1 in] Centerline, Sealable, Black, Printed Circuit Board, Power & Signal, enetSEAL+

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings

Connector System: **Wire-to-Wire**Number of Positions: **2**Connector & Housing Type: **Housing for Male Terminals**Centerline (Pitch): **2.54 mm [.1 in]**Sealable: **Yes**

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Nominal Voltage Architecture	12 V, 24 V
------------------------------	------------

Body Features

Primary Product Color	Black
-----------------------	-------

Connector & Keying Code

A-A

Contact Features

Contact Size	1.2mm
Contact Type	Tab
Mating Tab Width	1.2 mm[.047 in]

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance



For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | **enetSEAL+**




Other Automotive Connector Accessories(3)



PCB Headers & Receptacles(4)

Customers Also Bought

TE Part #66361-3
III+ PIN,18-14,15AU/FL,LPTE Part #W3S-1939
WEDGE LOCK, 3P, PLG, BLU, STD, J1939, DTTE Part #160927-4
FF 250 REC 1.0-2.5MM2 TPPBTE Part #280919-4
FF 187 REC 0.5-1.5MM2 TPPBTE Part #2112045-2
SLIDE,FOR 26POS TAB HSGTE Part #1-1456426-5
4POS, MCON 1.2 CB REC 2p TL SEALEDTE Part #2325098-2
MNTG CLIP,ENETSEAL PLUSTE Part #2325098-6
MNTG CLIP,ENETSEAL PLUSTE Part #9-2348789-1
HD MATEnet 2+6 TAB ASSY, GRP E, FLANGEDTE Part #8-1419161-4
2X4 SEALED PERIMETER SEAL

Documents

Product Drawings

[ADAPTER,2POS,1.2X0.6,PIN HSG ASSY](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2325106-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2325106-1_A.3d_jgs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2325106-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English