



Sensors > Temperature Sensors > NTC Thermistors Sensors & Probes > NTC Thermistors > Model 44000 Series



NTC Sensor Type: **Epoxy Coated NTC Thermistor**

Lead Wire Length: **76 mm [2.992 in]**

Resistance (at 25°C): **10 kΩ**

β-Value(25/85): **3978 K**

Tolerance β-Value: **±0.4 %**

[All Model 44000 Series \(32\)](#)

Features

Product Type Features

NTC Sensor Type	Epoxy Coated NTC Thermistor
Tolerance β-Value	±0.4 %

Electrical Characteristics

β-Value(25/85)	3978 K
----------------	--------

Dimensions

Lead Wire Length	76 mm[2.992 in]
------------------	-----------------

Usage Conditions

Resistance (at 25°C)	10 kΩ
Operating Temperature Range	-80 - 75 °C[-112 - 122 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240)



Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | MEAS 44000



Customers Also Bought




TE Part # 3-640440-7
07P MTA100 CONN ASSY 22AWG RED



TE Part # DT04-3P-CE09
REC, 3P, BLK, E, XCAP



TE Part # 206795-3
AMPLIMITE,SKT CONT ASY,SZ 20




TE Part # 787614-1
BAT INT,INS ASY W/TAB,5P,10.8V



TE Part # 58514-1
PROCRIMP TL W/DIE MR26-18



TE Part # 746785-1
50 POS STR RLF,LOW PROFILE



TE Part # 787439-1
BATT INT,INSERT ASSY,5P,12.0V



TE Part # 173600-1
070 TYPE LOOSE PIECE TAB CONT



TE Part # 66331-8
III+ SKT,24-20,30AU/FL,STRIP



TE Part # 1924580-2
ASSEMBLY SOCKET LOOSE PC NICKE

Documents

Datasheets & Catalog Pages
TESS-ANDO-408-0000050

English

Model 44000 Series Datasheet

English

Model 44036 Datasheet

English