



Connectors > Automotive Connectors > Automotive Housings > AMPSEAL Receptacle Housings



Connector System: **Wire-to-Board**  
Number of Positions: **8**  
Connector & Housing Type: **Housing for Female Terminals**  
Centerline (Pitch): **4 mm [ .157 in ]**  
Sealable: **Yes**

[All AMPSEAL Receptacle Housings \(31\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Board
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	8
Number of Rows	3

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------



Nominal Voltage Architecture	250 V
Body Features	
Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	1
Contact Features	
Contact Type	Socket
Mating Pin Diameter	1.3 mm[.051 in]
Contact Current Rating (Max)	17 A
Mechanical Attachment	
Terminal Position Assurance	Yes
Strain Relief	Add By Accessory
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Centerline (Pitch)	4 mm[.157 in]
Usage Conditions	
Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 - 105 °C[-40 - 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Industry Standards	
Degree of Protection	IP67
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	280
Packaging Method	Box & Tray
Other	
Connector Position Assurance Capable	Yes



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM78-H342  
AMPSEAL PCB Vertical Headers



TE Part # CAT-J04-APHH  
AMPSEAL PCB Right-Angle Headers



TE Part # 2138529-1  
STRAIN RELIEF, 8 POSITION AMPSEAL



TE Part # 770678-1  
SEAL PLUG, AMPSEAL




TE Part # CAT-AM78-T273  
AMPSEAL Crimp Contacts: 1.3 mm




TE Part # 2373965-1  
CPA,AMPSEAL


Also in the Series | AMPSEAL




Automotive Connector Locks & Position Assurance(1)




Automotive Housings(31)



Automotive Terminals(8)



Connector Backshells(4)



Connector Seals & Cavity Plugs(2)



Internal I/O Connectors(1)



PCB Headers & Receptacles(119)

Customers Also Bought



TE Part # HD10-9-1939P-P080  
RECP ASM, J1939 TYPE 2



TE Part # 1011-227-0205  
BKSHL, 2P, BLK, PLG, ST, NW6/7.5/8.5 /10



TE Part # 1028-013-0805  
Backshells, DEUTSCH DTM



TE Part # 2371885-1  
35POS,AMPSEAL,SOC HSG ASSY,SLD, COD 1




TE Part # YHDP26-24-7SN-CL22  
PLG, 7P, BLK, N, 4AWG, THD, 4/16, S



TE Part # 2373965-1  
CPA,AMPSEAL



TE Part # 1-180905-0  
FF 250 REC HSG 1P NYLON NAT



TE Part # 284546-2  
MONO-SHAPE CONN 3 POS PCB



Documents

Product Drawings

8POS,AMPSEAL,SOC HSG ASSY,SLD,COD 1

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2371882-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2371882-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2371882-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English