

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2041020209](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: Wire-to-Wire VersaBlade Hybrid Plug Housing, 2 Circuits, Friction Lock, Glow-Wire Capable

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 2041020609-001 \(PDF\)](#)
[Product Specification 2041020609-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Housings
Series	204102
Application	Power, Wire-to-Wire
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	191128970778


Physical

Circuits (maximum)	2
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester Alloy
Net Weight	1.594/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2041020609-001
Product Specification	2041020609-000
Sales Drawing	2041020209-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[204102 Series](#)

Mates With

VersaBlade Plug Housing [204102-0609](#)

Use With

VersaBlade Crimp Terminals [35745](#) , [35746](#)

 TPA [35965](#)