



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Gasket**
Primary Product Material: **Closed Cell Sponge**
Primary Product Color: **Black**
Operating Temperature (Max): **107 °C [225 °F]**
Contains Lubricant: **No**

Features

Product Type Features

Connector Seal & Plug Type	Gasket
----------------------------	--------

Configuration Features

Number of Positions	12
---------------------	----

Body Features

Primary Product Material	Closed Cell Sponge
Primary Product Color	Black

Usage Conditions

Operating Temperature (Max)	107 °C[225 °F]
Operating Temperature Range	-57 - 107 °C[-70 - 225 °F]

Industry Standards

UL Flammability Rating	UL 94HBF
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Other



Contains Lubricant	No
--------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-J41-DDRC
DEUTSCH DT Receptacle Connectors




TE Part # CAT-D487-CH8172
DEUTSCH DT Series Housings & Connectors

Also in the Series | DEUTSCH DT



Automotive Connector Caps & Covers (19)



Automotive Connector Locks & Position Assurance(86)



Automotive Housings(654)



Connector Backshells(61)



Connector Seals & Cavity Plugs(6)




Connector Strain Relief(28)



Insertion & Extraction Tools(3)



Other Automotive Connector Accessories(28)



PCB Headers & Receptacles(105)

Customers Also Bought



TE Part # W12P
WEDGE LOCK, 12P, REC, GRN, DT



TE Part # DT04-12PA-CL06
DEUTSCH DT Receptacle Connectors



TE Part # 42282-1
FF 250 REC 18-14AWG BR LP



TE Part # 61300-1
SPLICE IS 10000-16000 .031 TPST



TE Part # HDP24-18-20PE-L017
DEUTSCH HDP20 Housings



TE Part # DT4P-L012-GKT
GASKET, 4P, BLK, DT/DTM



TE Part # DT8P-L012-GKT
GASKET, 8P, BLK, DT/DTM

Documents



Product Drawings

GASKET DT 12 WY FLD RC

English

CAD Files

Customer View Model

ENG_CVM_CVM_DT12-L012-GKT_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_DT12-L012-GKT_B.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_DT12-L012-GKT_B.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English