



Terminals & Splices > Splices



Splice Type: **Splice Accessory**

Sealable: **No**

Features

Product Type Features

Splice Type	Splice Accessory
Sealable	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 165154
PIDG REPAIR KIT

Customers Also Bought



TE Part #35364
TERMINAL,PIDG R 12-10 10



TE Part #T4071017041-001
M8.FMLE.PNLREAR.4POS.STR WIRE



TE Part #1-52266-0
TERMINAL R PG 4 3/8



TE Part #52043-2
TERMINAL R PG 4 10



TE Part #YCFX26W1108PZN0000
PLUG ASSY



TE Part #YDTS24W11-35SNV001
RECP ASSY



TE Part #47386
DAHT PG PIDG 26-16 ASSY



TE Part #1SNK900603R0000
JB85-3

TE Part #1SNA116951R1500
FEM8S



TE Part #1337769-5
50 OHM COAX BNC STR PLUG P99-E

Documents

Product Drawings
PIDG/PG. INTRO.KIT
English