

COAXIAL CONNECTOR, BMA, 50 Ohm, Straight panel cable jack (female), flange mount

25_BMA-50-3-3/119_N

Properties

- Offers a range of floating configurations
- High reliability and ease of assembly
- Intermatable with the OSP connectors series
- Applicable in frequencies up to 18 GHz



Product configuration

Interface type	Gender	Standard
BMA	jack	IEC 60169-33_MIL-STD-348A/321

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Stainless Steel	
Insulator	PFA / PTFE	
Crimp ferrule	Brass	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data

Weight	0.0062 kg
Mating cycles	1000
Cable entry centre contact	soldered
Cable entry outer contact	crimped

Environmental data

Operation temperature	-65 °C ... 125 °C
-----------------------	-------------------

COAXIAL CONNECTOR, BMA, 50 Ohm, Straight panel cable jack (female), flange mount

25_BMA-50-3-3/119_N

Ordering Information Table		
Item number	Item description	Packaging type
22645619	25_BMA-50-3-3/119_NE	Single
Suitable cables		
Cable group	U9 - 3 mm / 50 Ohm	
	U11 - 3 mm / 50 Ohm	
Suitable cables	RG_223_/U	
	RG_142_B/U	
	ENVIROFLEX_142	
Additional Information		
Only as assembly	No	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2518 / Date of publication: 12.08.2024 / uncontrolled copy