



Connectors > Automotive Connectors > Automotive Housings > AMPSEAL Receptacle Housings



Connector System: **Wire-to-Board**

Number of Positions: **35**

Connector & Housing Type: **Housing for Female Terminals**

Centerline (Pitch): **4 mm [.16 in]**

Sealable: **Yes**

[All AMPSEAL Receptacle Housings \(31\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector System	Wire-to-Board
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	35
Number of Rows	3

Electrical Characteristics

Nominal Voltage Architecture	250 V
------------------------------	-------



Body Features

Primary Product Color	Black
Connector & Keying Code	1

Contact Features

Contact Type	Socket
Mating Pin Diameter	1.3 mm[.051 in]
Contact Current Rating (Max)	11 A

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	4 mm[.16 in]
--------------------	--------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 - 105 °C[-40 - 221 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IP6K7
----------------------	-------

Packaging Features

Packaging Quantity	140
Packaging Method	Box & Tray

Other

Connector Position Assurance Capable	Yes
--------------------------------------	-----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2024 (240)
Candidate List Declared Against: JAN 2024 (240)
SVHC > Threshold:
Octamethylcyclotetrasiloxane (D4) (.5% in Component Part)
Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part)
Decamethylcyclopentasiloxane (D5) (.5% in Component Part)

Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-J04-APHH
AMPSEAL PCB Right-Angle Headers




TE Part # CAT-AM78-H342
AMPSEAL PCB Vertical Headers




TE Part # 770678-1
SEAL PLUG, AMPSEAL



TE Part # CAT-AM78-T273
AMPSEAL Crimp Contacts: 1.3 mm




TE Part # 2389807-1
STRAIN RELIEF, 35 POSITION
AMPSEAL



TE Part # 2373965-1
CPA, AMPSEAL




Also in the Series | AMPSEAL



Automotive Connector Locks & Position Assurance(1)



Automotive Housings(31)



Automotive Terminals(8)




Connector Backshells(4)



Connector Seals & Cavity Plugs(2)



Internal I/O Connectors(1)



PCB Headers & Receptacles(119)

Customers Also Bought



TE Part # HDP24-24-16SE
REC, 16P, BLK, E, 12, S



TE Part # 1-1670901-1
12POS,AMP MCP2.8,REC HSG,ASSY



TE Part # CB0934-000
FL2500 Heat Shrink Tubing



TE Part # 1437839-1
107322A=DBL XMAS TREE CLIP, BL



TE Part # 2098641-1
2POS, MCON 1.2 CB REC 2p SL SEALED



TE Part # 2098641-4
2POS, MCON 1.2 CB REC 2p SL SEALED



TE Part # 2292937-1
2POS,1.2X0.6,TAB HSG ASSY,SLD, COD A



TE Part # 063725P074
ES2000-NO.2-B9-0-43MM