






3D VIEW



RECOMMEND PCB LAYOUT(± 0.05)

NOTES:


1. MATERIAL:
 - 1.1. HOUSING: LCP,COLOR IS GRAY,HIGH TEMPERATURE PLASTIC;
 - 1.2. CONTACT: BRASS(H65 T=0.20mm);
 - 1.3. SHELL: BRASS(H65,T=0.50mm);
2. FINISH:
 - 2.1. TERMINAL:
CONTACT AREA: GOLD PLATED G/Fu";
SOLDER AREA: PLATED OVER TIN;
 - 2.2. SHELL: NI PLATED OVER ALL ;
4. ELECTRICAL:
 - 4.1. VOLTAGE RATING: 40 VAC RMS;
 - 4.2. CURRENT RATING: 0.5 AMP;
 - 4.3. CONTACT RESISTANCE: 30mΩ MAX.;
 - 4.4. WITHSTAND VOLTAGE: 500 VAC RMS
50(60)Hz,1MIN.;
 - 4.5. INSULATION RESISTANCE: 100MEGOHMS MIN
@500V DC;
5. MECHANICAL:
 - 5.1. MATING FORCE: 44.1N MAX.;
 - 5.2. UNMATING FORCE: 9.8N MIN;
 - 5.3. OPERATING LIFE: 10000 CYCLES MIN.;
6. ENVIRONMENTAL:
 - 6.1. STORAGE TEMPERATURE RANGE:-40°C~+85°C;
 - 6.2. OPERATION TEMPERATURE RANGE:-25°C~+70°C;
- 7.SALT SPRAY TEST:24H(Salt spray test 24hours for gold plated area and 8 hours for tin plated area)

UMJBATACNA

- Code: A01.
- Interface: Borderless.
- Lifetime: 10,000 cycles.
- Material: Copper plated with nickel.
- Type: Without pillar.
- Appearance size: 12.1mm.
- Mounting method: Four-pronged plug-in SMT.
- Specification: 19 pins.
- Series: HDMI female socket.

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
								GENERAL TOLERANCE	
								≥0~2<	±0.15
C	塑胶	LCP	1	灰色	DESIGN	WANGGUIFA	2020.06.12	≥2~5<	±0.25
B	端子	黄铜H65	1	焊接镀锡 接触镀金1U	CHECKED	ZHENGUILAN	2020.06.12	≥0~2<	±0.15
A	外壳	黄铜H65	1	镀 镍	APPROVED	LILIANJIANG	2020.06.14	≥5	±0.35

FIRST VIEW



The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

TITLE::

HDMI A TYPE SMT TYPE 19P

of DWG NO: UMJBA-P190321

PART NO: UMJBA1980021

MODEL NO: UMJBATACNA

NAME:

HDMI CONN

SAMZO COMPONENTS
Electronic switch and connector manufacturer