

[illegible]

REV	E.C.N NO.	CONTENT	CHK	DATE

NOTES1:

UL Standard

1. Use group	B	C	D
Rated Current	8A	/	8A
Rated Voltage	300V	/	300V

2.Torque value: M2.0, 1.77Lb.in

3.Wire range: 28~16AWG

IEC Standard

1.	Pollution Degree	3	2	2
	Overvoltage Category	III	III	I
	Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
	Rate Voltage(V)	160V	160V	250V
	Rate Current(A)	7A	7A	7A

2. Torque value: M2, 0.2Nm

3.wire range: $0.2 \sim 1.5 \text{ mm}^2$

NOTES2:

1.Housing: PA66 (UL94V-0)

2.Cover: PA66 (UL94 V-0)

3.Cage: Brass (Ni Plated)

4. Conductor: Copper alloy (Sn Plated)

5.Screw: Steel (M2.0,Zn Plated)

NOTES3:

1.Pitch: 3.81mm Poles: 02-24P

2.Stripping length: 7-8mm

3.Operating temperature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$

4.RoHS Compliance

How to order

MX15EDGRK - 3.81 - XXP - XXXX - XX - X - X

产品型号 间距 颜色: 板数 01:常规颜色 A-Z其他定制

灰色:GY 橙色:OE 02-99: 0:Y一字螺丝

蓝色:BU 红色:RD 定制颜色 1:S十字螺丝

黑色:BK 透明色:TT Cu:铜方块 2:P.S平头十字螺丝

绿色:GN 黄色:YW Fe:铁方块

白色:WE

Pitch Range In mm			Nominal Dimension Range In mm					—		
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL		NOTE	
DWG.	CKK	DATE	24.03.13	UNITS	MM	SHEET/OF	1 / 1	A
CHK.		DATE		SCALE	1 : 1	A4		
APP.		DATE		NAME	MX15EDGRK-3.81-XXP			
 CIXI MAIXU ELECTRONICS CO.,LTD. 慈溪市迈旭电子有限公司				DWGN0.				