Ordering number : ENN8334



ON Semiconductor DATA SHEET

2SJ645 — General-Purpose Switching Device Applications

Features

- · Low ON-resistance.
- 2.5V drive.
- · Ultrahigh-speed switching.

Specifications

Absolute Maximum Ratings at Ta=25°C

| Parameter | Symbol | Conditions | Ratings | Unit |
|-----------------------------|--------|------------------------|-------------|------|
| Drain-to-Source Voltage | VDSS | | -20 | V |
| Gate-to-Source Voltage | VGSS | | ±10 | V |
| Drain Current (DC) | ID | | -8 | Α |
| Drain Current (Pulse) | IDP | PW≤10μs, duty cycle≤1% | -32 | Α |
| Allowable Power Dissipation | D- | | 1 | W |
| | PD | Tc=25°C | 20 | W |
| Channel Temperature | Tch | | 150 | °C |
| Storage Temperature | Tstg | | -55 to +150 | °C |

Electrical Characteristics at Ta=25°C

| Parameter | Symbol | Conditions | Ratings | | | 1.134 |
|--|-----------------------|---|---------|-----|------|-------|
| | | | min | typ | max | Unit |
| Drain-to-Source Breakdown Voltage | V(BR)DSS | I _D =-1mA, V _G S=0V | -20 | | | V |
| Zero-Gate Voltage Drain Current | IDSS | V _{DS} =-20V, V _{GS} =0V | | | -1 | μΑ |
| Gate-to-Source Leakage Current | IGSS | VGS=±8V, VDS=0V | | | ±10 | μΑ |
| Cutoff Voltage | VGS(off) | V _{DS} =-10V, I _D =-1mA | -0.4 | | -1.4 | V |
| Forward Transfer Admittance | yfs | V _{DS} =-10V, I _D =-4A | 5.6 | 8 | | S |
| Static Drain-to-Source On-State Resistance | RDS(on)1 | ID=-4A, VGS=-4.5V | | 55 | 72 | mΩ |
| | R _{DS} (on)2 | I _D =-2A, V _G S=-2.5V | | 77 | 108 | mΩ |
| Input Capacitance | Ciss | V _{DS} =-10V, f=1MHz | | 680 | | pF |
| Output Capacitance | Coss | V _{DS} =-10V, f=1MHz | | 115 | | pF |
| Reverse Transfer Capacitance | Crss | V _{DS} =-10V, f=1MHz | | 80 | | pF |
| Turn-ON Delay Time | t _d (on) | See specified Test Circuit. | | 12 | | ns |
| Rise Time | t _r | See specified Test Circuit. | | 120 | | ns |
| Turn-OFF Delay Time | t _d (off) | See specified Test Circuit. | | 55 | | ns |
| Fall Time | tf | See specified Test Circuit. | | 65 | | ns |


Continued on next page.

Continued from preceding page.

| Parameter | Symbol | Conditions | Ratings | | | Unit |
|-------------------------------|--------|--|---------|------|------|------|
| | | | min | typ | max | Oill |
| Total Gate Charge | Qg | V _{DS} =-10V, V _{GS} =-4.5V, I _D =-8A | | 8.7 | | nC |
| Gate-to-Source Charge | Qgs | V _{DS} =-10V, V _{GS} =-4.5V, I _D =-8A | | 1.5 | | nC |
| Gate-to-Drain "Miller" Charge | Qgd | V _{DS} =-10V, V _{GS} =-4.5V, I _D =-8A | | 1.8 | | nC |
| Diode Forward Voltage | VSD | IS=-8A, VGS=0V | | -1.0 | -1.5 | V |


Package Dimensions

unit : mm 7518-004





Package Dimensions


unit : mm 7003-004





Switching Time Test Circuit














ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or use of any product or circuit; and specifically discladims any and all liability, including without limitation special, consequential or incidental damages. SCILLC sasume any liability arising out of the applications or use of any product or circuit; and specifically discladims any and all liability, including without limitation special, consequential or incidental damages. SCILLC storage of any products and recommends adopting safety measures when designing equipment to avoid accidents or malfunctions. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals," must be validated for each customer application by customer's technical experts. SCILLC shall not be held liable for any claim or suits with regard to a third party's intellectual property rights which has resulted from the use of the technical information and products mentioned above. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC products could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affi liates, and distributors ha

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA

Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada

Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada

Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada.

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5773-3850 ON Semiconductor Website:www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative