

AMPLIMITE

TE Internal #: 204519-2


Plug, Cable-to-Cable, 62 Position, 4 Connector Shell Size, Pin, Size

22 Contact Size, 2.29 mm [.09 in] Centerline, Box Mount D-Sub

Connectors

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors

Connector & Housing Type: **Plug**Connector System: **Cable-to-Cable**Number of Positions: **62**Power/Signal/Coax Combination: **No**Connector Shell Size: **4**

Features

Product Type Features

Connector & Housing Type	Plug
Connector System	Cable-to-Cable
Connector Shell Size	4
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	62
Power/Signal/Coax Combination	No

Body Features

Rear Shell Material	Steel
Rear Shell Plating Material	Cadmium
Front Shell Plating Material	Cadmium
Mating Retention Feature Material	Stainless Steel
Front Shell Material	Steel

Contact Features

Contact Options	Supplied – Uninstalled
	50 μ in
Contact Mating Area Plating Material	Gold

Contact Base Material	Copper Alloy
Contact Type	Pin
Contact Size	Size 22
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mounting Hole Diameter	3.17 mm [.125 in]
Connector Mounting Type	Panel Mount
Mating Alignment	Without

Housing Features

Centerline (Pitch)	2.29 mm [.09 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (1.5% in Component Part) Cd (99.5% in Component Part)
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.

Article Safe Usage Statements:
Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 204370-2
PIN CONTACT, S22D, 22-28 AWG



TE Part # 91067-1
INSERTION/EXTRACTION TOOL

Customers Also Bought



TE Part #D369-P33-NP0
369 3 WAY PLUG, NO CONTACTS,
PIN



TE Part #1-6609028-8
10VK6=F7356 SO



TE Part #3-87499-7
20 MODIV HSG SR MRKD .100CL



TE Part #102107-2
MOD IV PIN LP



TE Part #1589700-1
SSM051B2H = SMT CONN



TE Part #1757824-8
AMPLIMITE, ASY, PLUG, STD, 90, ZN, 2,
CONT



TE Part #207683-8
AMPLIMITE, PIN CONT, SZ 22D



TE Part #87499-9
05 MODIV HSG SR MRKD .100CL

Documents

Product Drawings

[AMPLIMITE, ASY, PLUG, STD, 90, 4](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_204519-2_L_c-204519-2-l.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_204519-2_L_c-204519-2-l.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_204519-2_L_c-204519-2-l.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1308940_Sec8_amplimite](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English