


RA Varistor Series



Agency Approvals

Agency	Agency Approval	Agency File Number
	UL1449	E320116

Additional Information



Datasheet



Resources



Samples

Description

The RA Series transient surge suppressors are varistors (MOVs) supplied in a low-profile box that features a precise seating plane to increase mechanical stability for secure circuit-board mounting. This feature makes these devices suitable for industrial applications critical to vibration. Their construction permits operation up to 125°C (ambient) without derating.

The RA Series are available in voltage ratings up to 275V  $V_{M(AC)RMS}$  and energy levels up to 140J. These varistors are used in automotive, motor-control, telecommunication, and military applications.

See RA Series Device Ratings and Specifications Table for part number and brand information.

Features

- Lead-free/RoHS compliant parts available (add suffix "x2749")
- Low profile outline with precise seating plane
- No derating up to 125°C ambient
- In-line leads
- Wide operating voltage range:  
 $V_{M(AC)RMS}$ : 4 – 275V  
 $V_{M(DC)}$ : 5.5 – 369V
- High energy absorption capability  $W_{TM}$  up to 140J
- 3 model sizes available A8, RA16, and RA22

Absolute Maximum Ratings

• For ratings of individual members of a series, see Device Ratings and Specifications chart

Continuous		RA8 Series	RA16 Series	RA22 Series	Units
<b>Steady State Applied Voltage:</b>					
AC Voltage Range ( $V_{M(AC)RMS}$ )		4 to 275	10 to 275	4 to 275	V
DC Voltage Range ( $V_{M(DC)}$ )		5.5 to 369	14 to 369	18 to 369	V
<b>Transients:</b>					
Peak Pulse Current ( $I_{TM}$ )					
For 8/20µs Current Wave (See Figure 2)		100 to 1200	1000 to 4500	2000 to 6500	A
Single Pulse Energy Range (Note 1)					
For 10/1000µs Current Wave ( $W_{TM}$ )		0.4 to 23	3.5 to 75	70 to 160	J
Operating Ambient Temperature Range ( $T_A$ )		-55 to +125	-55 to +125	-55 to +125	°C
Storage Temperature Range ( $T_{STG}$ )		-55 to +150	-55 to +150	-55 to +150	°C
Temperature Coefficient (a') of Clamping Voltage ( $V_C$ ) at Specified Test Current		<0.01	<0.01	<0.01	%/°C
Hi-Pot Encapsulation (COATING Isolation Voltage Capability) (Delectric must withstand indicated DC voltage for one minute per MIL-STD 202, Method 301)		5000	5000	5000	V
COATING Insulation Resistance		1000	1000	1000	MΩ

**CAUTION:** Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.


### RA Series Ratings & Specifications

Part Number	Brand	Maximum Rating (125°C)					Specifications (25°C)					
		Continuous		Transient			Varistor Voltage at 1mA DC Test Current			Max Clamping Volt V <sub>c</sub> (8/20μs)		Typical Capacitance
		V <sub>RMS</sub>	V <sub>DC</sub>	Energy (10/1000μs)	Peak Current (8/20μs)	Min						
		V <sub>M(AC)</sub>	V <sub>M(DC)</sub>	W <sub>TM</sub>	I <sub>TM</sub>	(V)	(V)	(V)	(V)	(A)	f = 1MHz	
(mm)	(V)	(V)	(J)	(A)	(V)	(V)	(V)	(V)	(A)	(pF)		
<b>RA8 Series</b>												
V8RA8	8R	4	5.5	0.4	150	6	8.6	11.2	22	5	3000	
V12RA8	12R	6	8	0.6	150	9	12.5	16	34	5	2500	
V18RA8	18R	10	14	0.8	250	16.2	18	19.8	42	5	2000	
V22RA8	22R	14	18 (Note 3)	10 (Note 2)	250	19.8	22	24.2	47	5	1600	
V27RA8	27R	17	22	1.0	250	24.3	27	29.7	57	5	1300	
V33RA8	33R	20	26	1.2	250	29.7	33	36.3	68	5	1100	
V39RA8	39R	25	31	1.5	250	35.1	39	42.9	79	5	900	
V47RA8	47R	30	38	1.8	250	42.3	47	51.7	92	5	800	
V56RA8	56R	35	45	2.3	250	50.4	56	61.6	107	5	700	
V68RA8	68R	40	56	3.0	250	61.2	68	74.8	127	5	600	
V82RA8	82R	50	66	4.0	1200	73.8	82	90.2	135	10	500	
V100RA8	100R	60	81	5.0	1200	90	100	110	165	10	400	
V120RA8	120R	75	102	6.0	1200	108	120	132	205	10	300	
V150RA8	150R	95	127	8.0	1200	135	150	165	250	10	250	
V180RA8	180R	115	153	10.0	1200	162	180	198	295	10	200	
V200RA8	200R	130	175	11.0	1200	184.5	205	225.5	340	10	180	
† V220RA8	220R	140	180	12.0	1200	198	220	242	360	10	160	
† V240RA8	240R	150	200	13.0	1200	216	240	264	395	10	150	
† V270RA8	270R	175	225	15.0	1200	243	270	297	455	10	130	
† V360RA8	360R	230	300	20.0	1200	324	360	396	595	10	100	
† V390RA8	390R	250	330	21.0	1200	351	390	429	650	10	90	
† V430RA8	430R	275	369	23.0	1200	387	430	473	710	10	80	
<b>RA16 Series</b>												
V18RA16	18R16	10	14	3.5	1000	16.2	18	19.8	39	10	11000	
V22RA16	22R16	14	18 (Note 3)	50 (Note 2)	1000	19.8	22	24.2	43	10	9000	
V27RA16	27R16	17	22	5.0	1000	24.3	27	29.7	53	10	7000	
V33RA16	33R16	20	26	6.0	1000	29.7	33	36.3	64	10	6000	
V39RA16	39R16	25	31	7.2	1000	35.1	39	42.9	76	10	5000	
V47RA16	47R16	30	38	8.8	1000	42.3	47	51.7	89	10	4500	
V56RA16	56R16	35	45	10.0	1000	50.4	56	61.6	103	10	3900	
V68RA16	68R16	40	56	13.0	1000	61.2	68	74.8	123	10	3300	
V82RA16	82R16	50	66	15.0	4500	73.8	82	90.2	145	50	2500	
V100RA16	100R16	60	81	20.0	4500	90	100	110	175	50	2000	
V120RA16	120R16	75	102	22.0	4500	108	120	132	205	50	1700	
V150RA16	150R16	95	127	30.0	4500	135	150	165	255	50	1400	
V180RA16	180R16	115	153	35.0	4500	162	180	198	300	50	1100	
V200RA16	200R16	130	175	38.0	4500	184.5	205	225.5	340	50	1000	
† V220RA16	220R16	140	180	42.0	4500	198	220	242	360	50	900	
† V240RA16	240R16	150	200	45.0	4500	216	240	264	395	50	800	
† V270RA16	270R16	175	225	55.0	4500	243	270	297	455	50	700	
† V360RA16	360R16	230	300	70.0	4500	324	360	396	595	50	550	
† V390RA16	390R16	250	330	72.0	4500	351	390	429	650	50	500	
† V430RA16	430R16	275	369	75.0	4500	387	430	473	710	50	450	
<b>RA22 Series</b>												
V24RA22	24R22	14	18 (Note 3)	100.0 (Note 2)	2000	21.6	24	26.4	43	20	18000	
V36RA22	36R22	23	31	160.0 (Note 2)	2000	32.4	36	39.6	63	20	12000	
† V200RA22	200R22	130	175	70.0	6500	184.5	205	225.5	340	100	1900	
† V240RA22	240R22	150	200	80.0	6500	216	240	264	395	100	1600	
† V270RA22	270R22	175	225	90.0	6500	243	270	297	455	100	1400	
† V390RA22	390R22	250	330	130.0	6500	351	390	429	650	100	1000	
† V430RA22	430R22	275	369	140.0	6500	387	430	473	710	100	900	

**Notes:**

1. Average power dissipation of transients not to exceed 0.25W for RA8 Series, 0.60W for RA16 Series, or 1.0W for RA22 Series.
  2. Energy ratings for impulse duration of 30ms minimum to one half of peak current value.
  3. Also rated to withstand 24V for 5 minutes.
  4. 10mA DC Test Current.
- † Under UL File No. E320116 as a recognized component. CSA approved File No. 91788.


**Power Dissipation Ratings**




Should transients occur in rapid succession, the average power dissipation required is simply the energy (watt-seconds) per pulse times the number of pulses per second. The power so developed must be within the specifications shown on the Device Ratings and Specifications table for the specific device. Furthermore, the operating values need to be derated at high temperatures as shown above. Because varistors can only dissipate a relatively small amount of average power they are, therefore, not suitable for repetitive applications that involve substantial amounts of average power dissipation.

**Maximum Clamping Voltage for 8mm Parts**


**V8RA8 - V68RA8**



**V82RA8 - V430RA8**



**Peak Pulse Current Test Waveform**




$O_1$  = Virtual Origin of Wave  
 $T$  = Time from 10% to 90% of Peak  
 $T_1$  = Rise Time =  $1.25 \times T$   
 $T_2$  = Decay Time

**Example** - For an  $8/20 \mu s$  Current Waveform:


$8 \mu s = T_1 = \text{Rise Time}$   
 $20 \mu s = T_2 = \text{Decay Time}$

**Repetitive Surge Capability for 8mm Parts**

**V8RA8 - V12RA8**



**V18RA8 - V68RA8**



**Repetitive Surge Capability for 8mm Parts**


**V82RA8 - V430RA8**



**Figure 7**

**Maximum Clamping Voltage for 16mm Parts**


**V18RA16 - V68RA16**



**Figure 8**


**Repetitive Surge Capability for 16mm Parts**

**V18RA16 - V68RA16**




**Figure 9**

**V82RA16 - V430RA16**



**Figure 10**

**V82RA16 - V430RA16**



**Figure 11**

### Maximum Clamping Voltage for 22mm Parts

V24RA22 - V36RA22




Figure 12

### Repetitive Surge Capability for 22mm Parts

V24RA22 - V36RA22




Figure 13

V200RA22 - V430RA22




Figure 14

V200RA22 - V430RA22





Figure 15

**NOTE:** If pulse ratings are exceeded, a shift of  $V_{N(DC)}$  (at specified current) of more than  $\pm 10\%$  could result. This type of shift, which normally results in a decrease of  $V_{N(DC)}$ , may result in the device not meeting the original published specifications, but it does not prevent the device from continuing to function, and to provide ample protection.


### Wave Solder Profile

<b>Reflow Condition</b>		Pb – Free assembly
<b>Pre Heat</b>	- Temperature Min (Ts(min))	150°C
	- Temperature Max (Ts(max))	200°C
	- Time (min to max) (ts)	60 – 180 secs
<b>Average ramp-up rate (Liquidus Temp (TL) to peak)</b>		5°C/second max
<b>TS(max) to TL - Ramp-up Rate</b>		5°C/second max
<b>Reflow</b>	- Temperature (TL) (Liquidus)	217°C
	- Temperature (tL)	60 – 150 seconds
<b>Peak Temperature (TP)</b>		250+0/-5°C
<b>Time within 5°C of actual peak Temperature (tp)</b>		20 – 40 seconds
<b>Ramp-down Rate</b>		5°C/second max
<b>Time 25°C to peak Temperature (TP)</b>		8 minutes Max.
<b>Do not exceed</b>		260°C

### Lead-free Profile



### Non Lead-free Profile




### Environmental Specifications

<b>Operating/Storage Temperature</b>	-55°C to +125°C / -55°C to +150°C
<b>Humidity Aging</b>	+85°C, 85% RH, 1000 hours, +/-10% Voltage
<b>Thermal Shock</b>	+85°C to -40°C 10 times, +/-10% Voltage
<b>Solvent Resistance</b>	MIL-STD-202, Method 215
<b>Moisture Sensitivity</b>	Level 1, J-STD-020

### Physical Specifications

<b>Lead Material</b>	Tin-Coated
<b>Soldering Characteristics</b>	Solderability per MIL-STD-202, Method 208
<b>Insulating Material</b>	Cured, flame retardant epoxy polymer meets UL94V-0 requirements.
<b>Device Labeling</b>	Marked with LF, voltage, amperage rating, and date code.

**Product Dimensions (mm)**



Symbol	RA8 Series	RA16 Series	RA22 Series
<b>A (max.)</b>	8.85 (0.348)	15.1 (0.594)	19.1 (0.752)
<b>D (max.)</b>	11.45 (0.450)	19.7 (0.776)	25.5 (1.004)
<b>e ± 1</b>	5 (0.197)	7.5 (0.295)	7.5 (0.295)
<b>E (max.)</b>	5.2 (0.205)	6.3 (0.248)	6.3 (0.248)
<b>n (max.)</b>	0.7 (0.027)	0.7 (0.027)	0.7 (0.027)
<b>Øb ± 0.05</b>	0.635 (0.025)	0.81 (0.032)	0.81 (0.032)
<b>Weight (typical)</b>	1 Gram	3.4 Grams	4.4 Grams
<b>X</b>	2.2 (0.087)	2.2 (0.087)	4.4 (0.173)
<b>Y (Typ.)</b>	3.1 +/- 0.5 (0.122 +/- 0.02)	6 +/- 1 (0.236 +/- 0.04)	8.9 +/- 1 (0.35 +/- 0.04)
<b>Z (min.)</b>	0.4 (0.015)	0.8 (0.031)	0.8 (0.031)

**NOTES:** Dimensions are in mm, with dimensions in inches in parentheses. Inches for reference only.

**Part Numbering System**

The RA Series is supplied in bulk pack.

