



Connectors > Power Connectors > Circular Power > Circular Power Connectors > CPC Connectors, Series 2



Connector Product Type: **Housing**
Operating Voltage: **250 VDC**
Connector System: **Wire-to-Panel**
Number of Positions: **8**
Sealable: **No**

[All CPC Connectors, Series 2 \(23\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	8
Number of Power Positions	0
Number of Signal Positions	8

Electrical Characteristics

--	--



Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	Yes
Contact Type	Socket
Contact Current Rating (Max)	7.5 A
Contact Protection	With

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Panel Mount Feature Type	Flange with Mounting Holes
Mating Retention Type	Threaded Coupling
Thread Size	5/8-24 UNEF-2A
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	11

Dimensions

Compatible Insulation Diameter Range	1.73 mm[.068 in]
--------------------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 - 105 °C[-67 - 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	100
--------------------	-----



Packaging Method	Standard
------------------	----------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM71-C83998B
CPC Cable Clamps



TE Part # 206434-1
CPC PLUG ASSEMBLY SIZE 11-8




TE Part # 207489-1
FLEXIBLE CABLE BOOT, SIZE 11



TE Part # 207490-1
CABLE GRIPPER, SIZE 11




 TE Part # 213811-1 COUPLING RING,SZ 11,CPC	 TE Part # 207299-1 PLUG MTG. FLANGE NO 11 CPC	 TE Part # 206433-5 CPC RECPT,SZ 11-8,SMALL PACK	 TE Part # 2387131-1 PLUG CONN CA,REV,SER 2,SZ 11-8,L 0.5 M
 TE Part # 2387131-2 PLUG CONN CA,REV,SER 2,SZ 11-8,L 1M	 TE Part # 2387131-3 PLUG CONN CA,REV,SER 2,SZ 11-8,L 2M	 TE Part # 1-2407269-2 CAP, CPC, SIZE 11 RECP & 13 PLUG, BLACK	 TE Part # 1-2407269-1 CAP, CPC, SIZE 11 RECP & 13 PLUG, ORANGE
 TE Part # 1-2407269-3 CAP, CPC, SIZE 11 RECP & 13 PLUG, RED	 TE Part # 1-2407269-4 CAP, CPC, SIZE 11 RECP & 13 PLUG, YELLOW		

Also in the Series

AMP CPC

 Circular Power Connectors(458)	 Connector Backshells(1)	 Connector Caps & Covers(16)	 Connector Contacts(6)
 Connector Hardware(12)	 Connector Seals & Cavity Plugs(36)	 Connector Strain Relief(60)	 Insertion & Extraction Tools(1)



Customers Also Bought

TE Part # 206433-2
CPC RECPT ASSEMBLY SIZE 11-8

TE Part # 206429-1
CPC PLUG ASSY, 11-4, REV SEX

TE Part # 211398-1
Cable/Panel Mount Connector, CPC Series 1

TE Part # 66569-3
20DF SOCKET CONT. L.P.

TE Part # 644753-6
06P MTA156 HDR ASSY RN STR F/L

TE Part # 5-1393766-3
R10-E1Y4-V185=R10

TE Part # 1-2316531-3
AV19 DPM 3A MOVING RING R&G 12V

TE Part # 66587-1
TYPE VI PIN CONT,M-MATE,L.P.

Documents

Product Drawings
CPC RECPT ASSEMBLY SIZE 11-8
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_206433-1_U.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_206433-1_U.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_206433-1_U.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
AMP Circular Connectors for Commercial Signal & Power Applications
English

Instruction Sheets
Instruction Sheet (U.S.)
English

Agency Approvals
UL Report
English