



Connectors > Pluggable IO Connectors & Cages



Pluggable I/O Product Type: **Cage**

Sealable: **No**

Circuit Application: **Signal**

Number of Ports: **1**

Port Matrix Configuration: **1 x 1**

Features

Product Type Features

Cage Type	Single
Pluggable I/O Product Type	Cage
Sealable	No
Form Factor	QSFP+

Configuration Features

Number of Rear EONs per Port Column	2
Number of Ports	1
Port Matrix Configuration	1 x 1

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Termination Features

Termination Post & Tail Length	1.9 mm[.075 in]
Termination Method to PCB	Through Hole - Solder

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Dimensions

PCB Thickness (Recommended)	1.45 mm[.057 in]
-----------------------------	------------------



Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Heat Sink Compatible	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-C11-H50111
QSFP-Four SFP+ I/O Cable Assembly
30 AWG

TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP

TE Part # 2110819-1
QSFP+ Enh EVERCLEAR PT Conn

TE Part # 1-2053638-6
C/A, QSFP, 0.5M, P1-P2,
UNEQUALIZED

TE Part # CAT-C11-H5011
QSFP-Four SFP+ I/O Cable Assembly
28 AWG

TE Part # CAT-C11-H5011142
QSFP to QSFP I/O Cable Assembly: 33
AWG

TE Part # 2202165-4
QSFP TO QSFP, 26AWG, FDR, 4.0
METER

TE Part # 2202165-5
QSFP TO QSFP, 26AWG, FDR, 5.0
METER

TE Part # 2829040-2
QSFP IB EDR, 33AWG, 1.0M

TE Part # 2829040-4
QSFP IB EDR, 30AWG, 1.0M

TE Part # 2829040-6
QSFP IB EDR, 30AWG, 2.0M

TE Part # 2829040-7
QSFP IB EDR, 26AWG, 2.0M

TE Part # 2829040-8
QSFP IB EDR, 26AWG, 3.0M

TE Part # 2821033-8
QSFP TO [4]SFP+, 28G, 1M, 33AWG

Also in the Series | QSFP/QSFP+

Heat Sinks(1)





Light Pipes(8)

Pluggable I/O Cable Assemblies(13)

Pluggable IO Connectors & Cages(154)



Customers Also Bought

 TE Part #2007194-1 SFP+ 1x1 Cage Assembly, PCI, Solder Tail	 TE Part #6368168-4 2X1 OFFSET MJ,LED(G/Y,G/Y)12PN	 TE Part #1761987-9 ReceptacleConnAssm38PosTape/Re	 TE Part #1-1879214-9 CPF 0402 499R 0.1% 25PPM 1K RL
 TE Part #1825955-6 FSM3JH=6MM TACT SWITCH, HT W /ESD	 TE Part #2170567-7 1X4 QSFP KIT ASSY W/ LP, CUSTOMERIZED HS	 TE Part #2204430-2 MULTI-BEAM HD VERTICAL REC. 2P+15S	 TE Part #6-2338495-1 CAGE ASSEMBLY, 2 LP PER PORT, 1X4, OSFP
 TE Part #2159965-1 CA, 2POS ET TO RING TONGUE	 TE Part #2356580-2 SOCKET P4 TFLM KIT W/ COVER		

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_2110487-1_1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2110487-1_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2110487-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

