

S11MOC-P10MCC0-5220  
medi\_snap  
type\_s1



General information

|                   |                     |
|-------------------|---------------------|
| Part number       | S11MOC-P10MCC0-5220 |
| Termination       | solder              |
| Size              | 1                   |
| Locking principle | push                |
| Coding            | 0_key               |
| Cable Diameter    | cable_medi_52       |
| Cable outlet      | standard            |



Illustrations may differ from original product.  
Dimensions, unless otherwise specified, in mm.

**CODING:** 0 °

**POSITIONS:** 10 Positions

**DIMENSIONS**

The pin layout corresponds to the view on the termination area

Contact insert description

|                      |        |
|----------------------|--------|
| Number of contacts   | 10     |
| Contact type         | pins   |
| Contact diameter     | 05mm   |
| Insulator material   | peek   |
| Wire cross section   | 28_awg |
| Termination          | solder |
| Termination diameter | 045mm  |

reverse\_gender\_on\_request

Technical information

|                                          |          |               |
|------------------------------------------|----------|---------------|
| Max. creepage and air clearance distance | 05_mm    |               |
| Nominal current single contact           | 04_a     | iec_60512_5_2 |
| Nominal current insert                   | 2,2 A    | vde_0298_4    |
| Test voltage                             | 06_kv_ac | eia_364_20f   |

safety\_text

**Mechanical and environmental data**

|                       |          |
|-----------------------|----------|
| Degree of protection* | ip50     |
| Operating temperature | 50_120_c |
| Mating cycles         | 2000     |

mated\_unmated

**Material and surface treatments**

|              |               |
|--------------|---------------|
| Housing      | m_chrome      |
| Color option | red           |
| Contact      | cu_alloy_gold |

safety\_text\_2  
ul\_text  
illustrative\_text