




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Tin-Lead**

Contact Retention Within Housing: **With**

Contact Retention Type Within Housing: **Locking Lance**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Contact Features

Mating Pin Diameter	2.1 mm[.082 in]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Shape & Form	Round
Contact Orientation	Straight
Barrel Type	Open
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Tin-Lead
Contact Retention Within Housing	With
Contact Base Material	Brass

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Product Terminates To	Wire & Cable
Mechanical Attachment	
Wire Insulation Support	Without
Contact Retention Type Within Housing	Locking Lance
Dimensions	
Compatible Insulation Diameter Range	1.8 - 3.3 mm[.071 - .13 in]
Wire Size	.5 - 1 mm ²
Usage Conditions	
Operating Temperature Range	-55 - 105 °C
Operation/Application	
Circuit Application	Power
Packaging Features	
Packaging Quantity	500
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 465644-1 EXTRACTION TOOL	 TE Part # 455830-1 INSERTION TOOL	 TE Part # 1-171196-0 6 POS MATE-N-LOK S	 TE Part # 1-480274-0 09P CMNL PLUG HSG P/M NATL
 TE Part # 1-480284-0 08P CMNL CAP HSG M/M NATL	 TE Part # 1-480438-0 16P CMNL PLUG HSG M/M NATL	 TE Part # 1-480683-0 02P CMNL PLUG HSG F/H NATL	 TE Part # 1-480277-0 09P CMNL CAP HSG P/M NATL
 TE Part # 1-480722-0 04P CMNL PLUG HSG W/LCK NATL	 TE Part # 1-480276-0 06P CMNL CAP HSG P/M NATL	 TE Part # 1-480285-0 10P CMNL PLUG HSG M/M NATL	 TE Part # 1-480439-0 16P CMNL CAP HSG M/M NATL
 TE Part # 1-480393-1 02P CMNL PLUG HSG F/H BLK	 TE Part # 1-480345-0 08P CMNL CAP HSG F/H NATL	 TE Part # 1-480340-0 06P CMNL CAP HSG F/H NATL	 TE Part # 1-480278-0 12P CMNL CAP HSG P/M NATL



TE Part # 1-480425-0
04P CMNL PLUG HSG P/M NATL

TE Part # 1-480324-0
15P CMNL CAP HSG P/M NATL

TE Part # 1-480721-0
03P CMNL PLUG HSG W/LOK NATL

TE Part # 1-480323-0
15P CMNL PLUG HSG P/M NATL

Also in the Series | Commercial MATE-N-LOK

Connector Caps & Covers(2)

Connector Contacts(150)

Connector Seals & Cavity Plugs(1)

Crimp Wire Pins, Tabs & Ferrules(2)

Insertion & Extraction Tools(3)

Rectangular Connector Housings(9)

Rectangular Power Connectors(167)

Standard Circular Connectors(2)

Standard Rectangular Connectors(7)

Customers Also Bought

TE Part # 1-163036-0
6P.MATE-N-LOK HSG

TE Part # 1-480318-0
02P CMNL PLUG HSG F/H NATL

TE Part # 60394-1
RING TERMINAL 20-16 AWG BR

TE Part # 1676181-2
RN 0805 13K3 0.1% 10PPM 1KRL



 TE Part # ER52966001 RBK-ILS-125-NR1-0-38MM	 TE Part # 1-163035-0 6P.MATE-N-LOK HSG	 TE Part # YHC5932000000000000 BATTERY LEAD CONNECTOR.35MM. +VE.M6 THRD.	 TE Part # 154565 3 WAY PIN HOUSING M-N-L
---	--	--	--

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_163305-2_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_163305-2_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_163305-2_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.