

COAXIAL ADAPTER, BNC, 75 Ohm, Bulkhead, jack / jack (female / female)

34_BNC-75-0-5/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
BNC	jack (female)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120
BNC	jack (female)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Body		SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data	
Impedance	75 Ω
Interface frequency	3 GHz

COAXIAL ADAPTER, BNC, 75 Ohm, Bulkhead, jack / jack (female / female)
34_BNC-75-0-5/133_N

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 1 GHz	35 dB	1.04
1 GHz ... 2 GHz	24 dB	1.13
2 GHz ... 3 GHz	23 dB	1.15
Mechanical data		
Weight	0.0161 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-65 °C ... 165 °C	
Ordering Information Table		
Item number	Item description	Packaging type
84095130	34_BNC-75-0-5/133_NE	Single
Additional Information		
Remarks	True 75 ohm impedance	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2121 / Date of publication: 12.04.2024 / uncontrolled copy