



Connectors > PCB Connectors > PCB Headers & Receptacles



Connector System: **Bus Bar-to-Wire**
Number of Positions: **2**
Number of Rows: **1**
Centerline (Pitch): **36 mm [1.417 in]**
Termination Method to Printed Circuit Board: **Through Hole - Screw**

Features

Product Type Features

Connector System	Bus Bar-to-Wire
Header Type	Header & Push-Push Assembly
Sealable	Yes
Connector & Contact Terminates To	Bus Bar

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	1000 VAC
-------------------	----------

Body Features

Connector & Keying Code	AB
Primary Product Color	Black

Contact Features

--	--



Mating Pin Diameter	10 mm[.393 in]
Contact Mating Area Plating Material	Silver
Contact Type	Pin
Contact Current Rating (Max)	500 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Screw
---	----------------------

Mechanical Attachment

Mating Alignment Type	Polarization
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	36 mm[1.417 in]
--------------------	-----------------

Usage Conditions

Operating Temperature (Max)	140 °C[284 °F]
Operating Temperature Range	-40 - 140 °C[-40 - 284 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Degree of Protection	IPX9K
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part)












Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2394085-1 Pre-ASSY,Finger Access,Code K	 TE Part # 1-2394085-2 Pre-ASSY,Finger Access,Code L	 TE Part # 1-2394085-3 Pre-ASSY,Finger Access,Code M	 TE Part # 2-2394085-1 Pre-ASSY,Tool Access,Code A
 TE Part # 2-2394085-2 Pre-ASSY,Tool Access,Code B	 TE Part # 2-2394085-3 Pre-ASSY,Tool Access,Code C	 TE Part # 2-2394085-4 Pre-ASSY,Tool Access,Code D	 TE Part # 2-2394085-5 Pre-ASSY,Tool Access,Code E
 TE Part # 2-2394085-6 Pre-ASSY,Tool Access,Code F	 TE Part # 2-2394085-7 Pre-ASSY,Tool Access,Code G	 TE Part # 2-2394085-8 Pre-ASSY,Tool Access,Code H	 TE Part # 2-2394085-9 Pre-ASSY,Tool Access,Code J





TE Part # 2394085-2
Pre-ASSY, Finger Access, Code B



TE Part # 2394085-3
Pre-ASSY, Finger Access, Code C



TE Part # 2394085-4
Pre-ASSY, Finger Access, Code D



TE Part # 2394085-5
Pre-ASSY, Finger Access, Code E



TE Part # 2394085-6
Pre-ASSY, Finger Access, Code F



TE Part # 2394085-7
Pre-ASSY, Finger Access, Code G



TE Part # 2394085-8
Pre-ASSY, Finger Access, Code H



TE Part # 2394085-9
Pre-ASSY, Finger Access, Code J

Also in the Series | PowerTube HVP-HD 1000



Automotive Connector Caps & Covers
(3)



Automotive Connector EMC Shielding
(10)



Automotive Housings(24)




Automotive Terminals(6)



Connector Seals & Cavity Plugs(3)



Other Automotive Connector
Accessories(6)



PCB Headers & Receptacles(180)

Customers Also Bought



TE Part # 2-1418362-1
62 POS MIXED HEADER CODB



TE Part # 1563190-1
2POS,TAB 1.6 X 0.6,TAB HSG,COD



TE Part # 2-34111-3
SOLIS R 22-16 COMM 22-18 MIL 8



TE Part # 2-1618396-7
EV200GAANA=RELAY, EV200 SPST-NO



TE Part # 4-1618413-9
EV600HSANM = CONTACTOR, SPST-NO 24V COIL

TE Part # 1670720-6
SLIDE, TAB HSG GROUP C

TE Part # 1-1456426-5
4POS, MCON 1.2 CB REC 2p TL SEALED

TE Part # 353376-3
SQUIB CONT 1MM PIN DIA SOCKET

TE Part # 1-2399606-3
1POS, HVP1400, ASSY, 180DEG, COD M

TE Part # 2399608-1
3POS, HVP1400, ASSY, 180DEG, COD A/B/C

Documents

Product Drawings

HEADER 90D, ASSY. 2POS, FRONT SIDE, CODE AB

English

CAD Files

Customer View Model

ENG_CVM_CVM_2394071-1_B.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2394071-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2394071-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HIVONEX CONNECTORS & CHARGING SOLUTIONS

English

Product Specifications

Application Specification

English