




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Cable-to-Cable, Cable-to-Panel**

Number of Positions: **104**

Centerline (Pitch): **3.81 mm [.15 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Cable-to-Cable, Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	104
Number of Power Positions	104
Number of Signal Positions	104
Number of Rows	8

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Contact Features

Contact Current Rating (Max)	13 A
------------------------------	------



Contact Retention Within Housing	With
Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Screw Mount
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	3.81 mm[.15 in]
Housing Color	Black
Housing Material	Polyester - GF

Dimensions

Connector Height	71.88 mm[2.83 in]
Product Width	28.7 mm[1.13 in]
Product Length	107.37 mm[4.227 in]
Wire Size	.05 - 2 mm ²
Row-to-Row Spacing	3.3 mm[.13 in]

Usage Conditions

Operating Temperature Range	-55 - 130 °C[-67 - 266 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 202169-4
M-SERIES HALF SHIELD KIT

Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(7)



Connector Caps & Covers(12)



Connector Hardware(18)




Connector Strain Relief(11)



Rack & Panel Connectors(1)



Rectangular Power Connectors(65)



Standard Edge Connectors(1)


Customers Also Bought



TE Part # 1-66359-6
III+ PIN,18-14,30AU/FL,STRIP



TE Part # 52935
TERMINAL,PIDG SPR SPD 16-14 6




TE Part # 747080-2
LATCH BLOCK/PACKAGED/.090 PANL



TE Part # 2329917-1
PWR VERSA-LOCK SEAL RECPT, 22-26AWG




TE Part # 1062-16-0622
SOC, SF, SIZE 16, 16-20, NI/SN



TE Part # 1-2112890-4
25POS, MIXED,TAB HSG,ASSY



TE Part # 2-1375820-2
CST-100 II HOUSING 22 POS



TE Part # 2-640550-2
22P MTA100 COVER



TE Part # 2-33466-3
TERMINAL,SOLIS R 6 5/16



TE Part # 770106-1
15P .093 COMM P&S PLUG

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-201692-6_AN.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-201692-6_AN.3d_igs.zip



English

Customer View Model

[ENG_CVM_1-201692-6_AN.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-201692-6_AY.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-201692-6_AY.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-201692-6_AY.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[M Series 104-Position Plug & Receptacle Connectors w/Center Fasteners](#)

English