

15KESS6BFPW

✓ ACTIVE

Corcom KES


TE Internal #: 4-1609966-4

3-Phase Filters, 15A Current Rating, Threaded Bolt Input, Threaded Bolt Output, WYE (4 wire + ground), Operating Voltage 520 VAC, Chassis, Corcom KES

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters



Current Rating: 15 A

Input Termination Type: Threaded Bolt

Output Termination Type: Threaded Bolt

Wiring Configuration: WYE (4 wire + ground)

Operating Voltage: 520 VAC

Features

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Threaded Bolt
Output Termination Type	Threaded Bolt

Configuration Features

Wiring Configuration	WYE (4 wire + ground)
----------------------	-----------------------

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	3
Current Rating	15 A
Operating Voltage	520 VAC

Mechanical Attachment

Product Mount Type	Chassis
--------------------	---------

Usage Conditions

Operating Temperature Range	-25 - 85 °C
-----------------------------	-------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Corcom KES

15KESS6BFPW

3-Phase Filters, 15A Current Rating, Threaded Bolt Input, Threaded Bolt Output, WYE (4 wire + ground), Operating Voltage 520 VAC, Chassis, Corcom KES



3-Phase Filters(38)

Customers Also Bought



TE Part # 2-644488-6
06P MTA100 SHRD HDR F/L R/A SN



TE Part # 535090-4
096 EURO TYPE C RECEPT ST ASSY




TE Part # 6-1393252-1
W67-X2Q12-30=M6/M7/M9/W6/W7



TE Part # 1-1393767-5
R10-E2X2-V700=R10



TE Part # 7-1625890-0
2W SM M/OX 5% 82K



TE Part # 1-1393766-9
R10-E1X4-24V=R10

Documents

Product Drawings

KES 15A 1S NUT WYE 520VAC

English

CAD Files

Customer View Model

ENG_CVM_CVM_4-1609966-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1609966-4_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_4-1609966-4_B.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

15KESS6BFPW

3-Phase Filters, 15A Current Rating, Threaded Bolt Input, Threaded Bolt Output, WYE (4 wire + ground), Operating Voltage 520 VAC, Chassis, Corcom KES



Datasheets & Catalog Pages

KES SERIES

English