



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Black**

Primary Product Material: **Nylon**

Number of Positions: **36**

Operating Temperature (Max): **85 °C [185 °F]**

Features

Product Type Features

Sealable	No
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	36
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Usage Conditions

Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-55 - 85 °C[-67 - 185 °F]

Packaging Features

Packaging Quantity	100
--------------------	-----



Packaging Method

Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Customers Also Bought




TE Part # 284743-1
94POS MIXED MQS REC SEALED



TE Part # 1-640526-0
36P MR II PLUG HSG V0




TE Part # 770028-1
09P UMNLI IN-LINE CAP HSG KIT



TE Part # 280289
MODULAR RELAY CONN.



TE Part # 41582
RING 190(4.82 MM) 24-20 AWG TPBR



TE Part # 641294-1
MR RECPT 26-18 PTPHBZ



TE Part # 1658658-1
KIT,HDP-20,ENCLSUR,RCPT,SIZE 3



TE Part # 1-962842-1
TAB 2.8x0.8 CONTACT CS SRC Sn



TE Part # 172494-1
MIC MARK-2 PLUG HSG 5P



TE Part # 710026-5
XCT 25-8

Documents

Product Drawings

36P STR/REL HNGD

English

CAD Files

Customer View Model

ENG_CVM_1-480594-9_P.3d_igs.zip

English

Customer View Model

ENG_CVM_1-480594-9_P.3d_stp.zip

English

Customer View Model

ENG_CVM_1-480594-9_P.2d_dxf.zip

English

3D PDF

English

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-480594-9_AG.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-480594-9_AG.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-480594-9_AG.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[AMP* MINIATURE RECTANGULAR II \(MRII\) CONNECTORS](#)

English