




Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Position Assurance**

Connector Hardware Accessory Type: **TPA (Terminal Position Assurance)**

Primary Product Color: **Black**

Primary Product Material: **Glass-Filled PBT**

Operating Temperature (Max): **140 °C [284 °F]**

Features

Product Type Features

Hardware Accessory Function	Position Assurance
Connector Hardware Accessory Type	TPA (Terminal Position Assurance)

Body Features

Primary Product Color	Black
Primary Product Material	Glass-Filled PBT

Usage Conditions

Operating Temperature (Max)	140 °C[284 °F]
Operating Temperature Range	-30 - 140 °C[-22 - 284 °F]

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Bag
------------------	-----



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2381608-6 Power Versa-Lock TNL CAP, 2X3 KEY A, GWT	 TE Part # 1-2336229-6 Power Versa-Lock PLUG, 2X3 KEY A	 TE Part # 1-2336231-6 Power Versa-Lock TNL CAP, 2X3 KEY A	 TE Part # 1-2337219-6 Power Versa-Lock CAP, 2X3 KEY A
 TE Part # 2-2336229-6 Power Versa-Lock PLUG, 2X3 KEY B	 TE Part # 2-2336231-6 Power Versa-Lock TNL CAP, 2X3 KEY B	 TE Part # 3-2336229-6 Power Versa-Lock PLUG, 2X3 KEY C	 TE Part # 3-2336231-6 Power Versa-Lock TL CAP, 2X3 KEY C



TE Part # 2-2337219-6
PWR VERSA-LOCK CAP, 2X3 KEY B

TE Part # 3-2337219-6
PWR VERSA-LOCK CAP, 2X3 KEY C

Also in the Series

Power Versa-Lock 5.0

Connector Caps & Covers(3)

Connector Contacts(12)

Connector Hardware(5)

Connector Seals & Cavity Plugs(9)

Insertion & Extraction Tools(2)

Rectangular Power Connectors(77)

Customers Also Bought

TE Part # 177898-1
STD Temp Power Double Lock Plug

TE Part # 794896-1
2 CIR MINI UMNL RND WIRE HOLES

TE Part # 1-1644055-2
UMNL 6 WAY PLUG HOUSING

TE Part # 794991-1
02P UMNL BLACK INTERFACE SEAL

TE Part # 1586847-1
03P UMNL PLUG HSG, GW

TE Part # 794714-1
06P UMNL CAP HSG NATL,PAN MNT

TE Part # 1969825-6
EP 2.5 TPA RETAINER, 6 POS

TE Part # 2238266-1
Housing 1 position POSI-LOCK, 250 Series



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2337218-6_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2337218-6_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2337218-6_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English